

**Cable Tie**  
**T&B Catalog Number:**

TYD5135M

**UPC Number:**

78621071342

**Status:**

Active

**Description:**

Cable Tie Deltec 1/2 in. x 14 Double-locking head

**Features**

Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.

Strap and body are weatherable acetal, offering superior resistance to sunlight, moisture and salt environments.

Locking device is marine-grade corrosion-resistant copper alloy.

**Application**

Ideal solution for bundling in harsh outdoor environments.

**General**

Material	Weather-Resistant Acetal
Color	Black

**Dimension Information**

Nominal Length (inches)	14
Length (inches)	13.5
Width (inches)	.500
Max. Wire Bundle Diameter (inches)	3.5

**Specifications**

Temperature Rating	-30°F to 150°F
--------------------	----------------

**Tooling**

Application Tools	WT3D
-------------------	------

**Packaging**

T&B Order Multiple	250
T&B Inner Pack	25
Package in Units	250
Package Type	Regular
T&B Sold in UOM	Each
T&B Weight Per UOM	3 lbs. per 100

**Application Support**

Overview	Available on Website
Material Selection Guide	Available on Website

**Notes**

The recommended maximum continuous static loading for the Deltec® straps is 20 lbs. Per strap. For best results suggested spacing is 15 inches. It is the responsibility of the user to determine whether or not their application meets our recommendation.

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:[techsupport@tnb.com](mailto:techsupport@tnb.com)