

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 526221

NOTE:-

- 1 MATERIAL:
HOUSING: 30% GLASS FILLED PBT, THERMOPLASTIC, BLACK.
CONTACT: PHOS BRONZE
- 2 FINISH: CONTACT PLATING: TIN-LEAD (60u INCHES MIN.)
SOLDERABILITY :95% COVERAGE MIN.;
TEST TEMPERATURE=230°C±5°C
TEST TIME = 5±5 SECONDS.
3. MECHANICAL SPECS:
DURABILITY: 50 CYCLES MIN.
INSERTION FORCE:300 GRAMS MAX.
WITHDRAWAL FORCE: 20 GRAMS MIN.
CONTACT RETENTION: 500 GRAMS MIN.
ACCEPTS: 0.20-0.30 [.008-.012] LEADS
4. ELECTRICAL SPECS:
VOLTAGE RATING: 250V AC,DC
CONTACT RESISTANCE: 20 MILLOHMS MAX.
CURRENT RATING: 1 AMPERE AC,DC
INSULATION RESISTANCE: 1000 MEGOHMS MIN.
DIELECTRIC WITHSTANDING VOLTAGE: AC 1000 V MIN.
5. OPERATING TEMPERATURE: -40°C TO +105°C
- 6 AMP LOGO
- 7 LADDER PRESENT FOR 24, 28 & 32 POSITION SOCKETS.
- 8 FINISH: CONTACT PLATING TIN (LEAD FREE); 60 UIN MIN. OVER 30 UIN Ni
SOLDERABILITY :95% COVERAGE MIN.;
TEST TEMPERATURE=260°±5°C;
TEST TIME = 5±5 SECONDS.

SECTION D-D

FINISH	POS	A ±0.20 [.008]	B±0.10 [.004]	C±0.15 [.004]	PART NO.
1	6	7.62 [.300]	5.08 [.200]	2.10 [.083]	390261-1
2	8	10.16 [.400]	7.62 [.300]	4.76 [.187]	390261-2
2	14	17.78 [.700]	15.24 [.600]	12.38 [.487]	390261-3
2	16	20.32 [.800]	17.78 [.700]	14.92 [.587]	390261-4
2	18	22.86 [.900]	20.32 [.800]	17.46 [.687]	390261-5
2	20	25.40 [1.000]	22.86 [.900]	20.00 [.787]	390261-6
2	22	27.94 [1.100]	25.40 [1.000]	22.54 [.887]	390261-7
2	24	30.48 [1.200]	27.94 [1.100]	25.10 [.988]	390261-8
2	28	35.56 [1.400]	33.02 [1.300]	30.12 [1.185]	390261-9
2	32	40.64 [1.600]	38.10 [1.500]	35.20 [1.386]	1-390261-0
8	6	7.62 [.300]	5.08 [.200]	2.10 [.083]	1-390261-1
8	8	10.16 [.400]	7.62 [.300]	4.76 [.187]	1-390261-2
8	14	17.78 [.700]	15.24 [.600]	12.38 [.487]	1-390261-3
8	16	20.32 [.800]	17.78 [.700]	14.92 [.587]	1-390261-4
8	18	22.86 [.900]	20.32 [.800]	17.46 [.687]	1-390261-5
8	20	25.40 [1.000]	22.86 [.900]	20.00 [.787]	1-390261-6
8	22	27.94 [1.100]	25.40 [1.000]	22.54 [.887]	1-390261-7
8	24	30.48 [1.200]	27.94 [1.100]	25.10 [.988]	1-390261-8
8	28	35.56 [1.400]	33.02 [1.300]	30.12 [1.185]	1-390261-9
8	32	40.64 [1.600]	38.10 [1.500]	35.20 [1.386]	2-390261-0