

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0460182541

Status:


Active

Overview:

Mini-Fit® Plus Connector System

Description:

Mini-Fit® Plus High Mating Cycle Female Crimp Terminal, 22-24 AWG, Reel, Select Gold (Au) Plating with Proprietary Molex Advanced Contact Surface Finish (CSF) in Contact Area



Documents:	
Drawing (PDF)	Test Summary TS-46018-001 (PDF)
Packaging Specification PK-46018-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	46018
Application	Power
Comments	Current Rating = 5A Max. Using 22 AWG Wire and 4A Max. Using 24 AWG Wire
Crimp Quality Equipment	Yes
Overview	Mini-Fit® Plus Connector System
Packaging Alternative	46018-2542 (Loose)
Product Name	Mini-Fit® Plus
UPC	822350560450
Physical	
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.150/g
Packaging Type	Reel
Plating min - Mating	0.051µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.20-1.80mm
Wire Size AWG	22, 24
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	13.0A
Voltage - Maximum	600V
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-46018-001
Sales Drawing	SD-46018-001
Test Summary	TS-46018-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Contains SVHC(2015

June 15): No

Halogen-Free

Status

Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

46018 Series

Use With

5557 Mini-Fit Jr.™ Receptacles, 30067 Mini-Fit® TPA Receptacles, 42474 Mini-Fit® BMI Panel Mount Receptacles, 44516 Mini-Fit® BMI Panel Mount Slide-N-Lock Receptacles

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

FineAdjust™

0639020200

Applicator for

Insulation OD

1.10-1.30mm - 22-28

AWG

FineAdjust™	0639002700
Applicator for	
Insulation OD	
1.30-1.50mm, 22-28	
AWG Wire	
Extraction Tool	0011030044
Hand Crimp Tool for	0638191000
Crimp Terminals	
FineAdjust™	0639023800
Applicator for	
Insulation OD	
0.95-1.08mm - 22-28	
AWG	
T2 Terminator™	0639102700
for insulation OD	
1.30-1.50mm - 22-28	
AWG	
T2 Terminator™	0639120200
for insulation OD	
1.10-1.30mm - 22-28	
AWG	
T2 Terminator™	0639123800
for insulation OD	
0.95-1.08mm - 22-28	
AWG	

This document was generated on 09/10/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION