

0301 KSS Nylon Cable Tie



• MATERIAL: Nylon 66.



※CVT-070 non min. bundle dia
 ※CV-200T tail
 ※CV-300STZ, 180T, 190T tail

Unit: mm

Item No.				L		W	Max. Bundle Dia.	Min Loop Tensile Strength	
Natural		Black							
100 pcs / Bag	1000 pcs / Bag	100 pcs / Bag	1000 pcs / Bag	mm	inch			lbs	kgs
CV-060	CV-060K	CV-060B	CV-060KB	63.7	2 1/2"	2.40	11	18	8
CVT-070	CVT-070K	CVT-070B	CVT-070KB	71.0	2 13/16"	1.60	11		
CV-075	CV-075K	CV-075B	CV-075KB	75.0	3"	2.40	15		
CV-080	CV-080K	CV-080B	CV-080KB	80.0	3 1/8"	2.50	16		
CV-094	CV-094K	CV-094B	CV-094KB	96.0	3 3/4"	2.50	21		
CV-100	CV-100K	CV-100B	CV-100KB	100.0	4"	2.50	22		
CVT-100	CVT-100K	CVT-100B	CVT-100KB	103.0	4"	1.95	22		
CV-120S	CV-120SK	CV-120SB	CV-120SKB	120.0	4 3/4"	2.50	28		
CV-140S	CV-140SK	CV-140SB	CV-140SKB	142.0	5 1/2"	2.50	35		
CV-150S	CV-150SK	CV-150SB	CV-150SKB	155.0	6 1/8"	2.50	39		
CV-165	CV-165K	CV-165B	CV-165KB	165.0	6 1/2"	2.50	43		
CV-200M	CV-200MK	CV-200MB	CV-200MKB	203.0	8"	2.50	55		
CV-250S	CV-250SK	CV-250SB	CV-250SKB	250.0	10"	2.50	68		
CV-300M	CV-300MK	CV-300MB	CV-300MKB	300.0	11 7/8"	2.50	80		
CV-400S		CV-400SB		400.0	15 3/4"	2.50	116		
CV-120	CV-120K	CV-120B	CV-120KB	120.0	4 3/4"	3.20	28	40	18
CV-140	CV-140K	CV-140B	CV-140KB	142.0	5 1/2"	3.20	34		
CV-150	CV-150K	CV-150B	CV-150KB	150.0	6"	3.60	36		
CV-180	CV-180K	CV-180B	CV-180KB	180.0	7"	3.60	46		
CV-180T	CV-180TK	CV-180TB	CV-180TKB	180.0	7"	3.60	46		
CV-200S	CV-200SK	CV-200SB	CV-200SKB	203.0	8"	3.20	53		
CV-200A	CV-200AK	CV-200AB	CV-200AKB	203.0	8"	3.60	52		
CV-250M	CV-250MK	CV-250MB	CV-250MKB	250.0	10"	3.60	68		
CV-265	CV-265K	CV-265B	CV-265KB	265.0	10 1/2"	3.60	73		
CV-292	CV-292K	CV-292B	CV-292KB	292.0	11 1/2"	3.60	82		
CV-330		CV-330B		330.0	13"	3.60	93		
CV-368S		CV-368SB		368.0	14 1/2"	3.60	105		
CV-120L	CV-120LK	CV-120LB	CV-120LKB	120.0	4 3/4"	4.80	27	50	22
CV-160L	CV-160LK	CV-160LB	CV-160LKB	160.0	6 1/4"	4.80	39		
CV-190	CV-190K	CV-190B	CV-190KB	190.0	7 1/2"	4.80	49		
CV-190T	CV-190TK	CV-190TB	CV-190TKB	190.0	7 1/2"	4.80	49		
CV-200	CV-200K	CV-200B	CV-200KB	203.0	8"	4.60	52		
CV-200D	CV-200DK	CV-200DB	CV-200DKB	203.0	8"	4.80	52		
CV-200T	CV-200TK	CV-200TB	CV-200TKB	203.0	8"	4.60	52		
CV-250	CV-250K	CV-250B	CV-250KB	250.0	10"	4.80	68		
CV-280	CV-280K	CV-280B	CV-280KB	280.0	11"	4.80	77		
CV-300S		CV-300SB		300.0	11 7/8"	4.80	83		
CV-310		CV-310B		310.0	12"	4.80	86		
CV-368		CV-368B		368.0	14 1/2"	4.80	105		
CV-385		CV-385B		385.0	15 3/16"	4.80	110		
CV-432		CV-432B		432.0	17"	4.80	125		
CV-450M		CV-450MB		450.0	17 3/4"	4.80	131		
CV-500		CV-500B		500.0	19 11/16"	4.80	147	120	55
CV-550S		CV-550SB		550.0	21 11/16"	4.80	162		
CV-610S		CV-610SB		610.0	24"	4.80	181		
CV-635S		CV-635SB		635.0	25"	4.80	189		
CV-914S		CV-914SB		914.0	36"	4.80	278		
CV-300STZ		CV-300STZB		300.0	11 7/8"	4.80	83	80	36
CV-380S		CV-380SB		380.0	15"	6.40	110	100	45
CV-120LL	CV-120LLK	CV-120LLB	CV-120LLKB	120.0	4 3/4"	7.60	22	175	80
CV-150L	CV-150LK	CV-150LB	CV-150LKB	150.0	6"	7.60	32		
CV-200L	CV-200LK	CV-200LB	CV-200LKB	203.0	8"	7.60	52		
CV-240L	CV-240LK	CV-240LB	CV-240LKB	240.0	9 7/16"	7.60	61		
CV-280L	CV-280LK	CV-280LB	CV-280LKB	280.0	11"	7.60	74		
CV-300		CV-300B		300.0	11 7/8"	7.60	80		
CV-340		CV-340B		340.0	13 1/2"	7.60	92		
CV-380		CV-380B		380.0	15"	7.60	105		
CV-750		CV-750B		750.0	29 1/2"	7.50	223		
CV-380L		CV-380LB		380.0	15"	8.00	105		
CV-450		CV-450B		450.0	17 3/4"	8.00	128		
CV-500L		CV-500LB		500.0	19 11/16"	8.00	143		
CV-550		CV-550B		550.0	21 11/16"	8.00	160		
CV-610		CV-610B		610.0	24"	9.00	177		
CV-685		CV-685B		685.0	27"	9.00	202		
CV-710		CV-710B		710.0	28"	9.00	209		
CV-762		CV-762B		762.0	30"	9.00	227		
CV-812		CV-812B		812.0	32"	9.00	243		
CV-914		CV-914B		914.0	36"	9.00	275		
CV-940		CV-940B		940.0	37"	9.00	284		
CV-1168		CV-1168B		1,168.0	46"	9.00	356		
CV-1219		CV-1219B		1,219.0	48"	9.00	372		
CV-1500		CV-1500B		1,500.0	59"	9.00	462		