

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192520142

Status:

Active

Overview:

wire_management_products

Description:

299.72mm UV Black Cable Tie, 40 Pound Tensile Strength, 100/Bag

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Accessories
Series	19252
Application Tooling Part Link	192940002
Comments	Maximum bundle diameter = 87.12mm. Engineering Number N-11-40-0-C-LC
Component Type	Cable Tie
Overview	wire_management_products
Product Name	N/A
Physical	
Circuits (Loaded)	N/A
Lock to Mating Part	None
Packaging Type	Bag
Temperature Range - Operating	105°C
Material Info	
Old Part Number	N-11-40-0-C-LC
Reference - Drawing Numbers	
Sales Drawing	SD-19252-001



image - Reference only

Series

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19252Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
ServiceGrade™ Economy Cable Tie Tool	0192940002

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19252-0142