


3.5mm Mono Phone Plug

171-3302-EX



3.5mm Mono Phone Plug



Dimensions: In.

| SPECIFICATIONS | |
|-----------------------------|---------------------|
| Temperature Rating: | 80°C |
| Breakdown Voltage: | 500VAC for 1 Minute |
| Insulation Resistance: | 100MΩ @ 500VDC |
| Contact Resistance: | 50mΩ max. |
| Life Time: | 10,000 Cycles min. |
| RoHS Compliant by Exemption | |

| MATERIALS | | |
|-----------|-----------------|----------------------|
| Part No. | Part | Plating |
| 1 | Tip | Nickel Plated Brass |
| 2 | Insulator | ABS |
| 3 | Sleeve | Nickel Plated Brass |
| 4 | Tip Terminal | Nickel Plated Copper |
| 5 | Cap | PP |
| 6 | Sleeve Terminal | Nickel Plated Brass |

Date Last Revised: 12-21-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300888

171-3302-EX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-3302-EX](#)