

26P, 20P




28P, 22P, 16P

注 記

1. 適用コネクタ型番 : X-173977-X (リセ)

NOTE

1. CONNECTOR P/N : X-173977-X (REC)



34.3	26.0	14	30	3-176239-0
32.3	26.0	13	28	2- -8
30.3	24.0	12	26	2- -5
28.3	22.0	11	24	2- -4
26.3	20.0	10	22	2- -2
24.3	18.0	9	20	2- -0
22.3	16.0	8	18	1- -8
20.3	14.0	7	16	1-176239-6
A	B	N	POS 極数	型 番 P/N

Copyright ©1990
AMP (Japan), LTD.
ALL RIGHTS RESERVED.

AMP

Tokyo, Japan

ホルダ新面番 (WIRE RANGE) 電線外径 (INSULATION DIA.)

材料 (MATERIAL) 色 (COLOR)

6671000樹脂 黄色

DR. Y. KODAIRA 10-AUG-'90

CHK. H. KANAI 12/SEP/'90

APP. R. NISHIMURA 13/SEP/'90

DR. Y. KODAIRA 10-AUG-'90

CHK. H. KANAI 12/SEP/'90

APP. R. NISHIMURA 13/SEP/'90

HOLDER CT DOUBLE ROW CONN.

ホルダ新面番 CTダブルローコネクタ

一般公差 (GENERAL TOLERANCE)

100μm ±0.2

100μm ±0.25

100μm ±0.3

100μm ±0.3

100μm ±0.3

100μm ±0.3

100μm ±0.3

100μm ±0.3

100μm ±0.3

100μm ±0.3