




JKL LAMP NUMBER	VOLTS RATED	AMPS $\pm 10\%$	*MSCP $\pm 25\%$	*LUMENS $\pm 25\%$	AVERAGE LIFE HRS.	FILAMENT TYPE
SML0650	6.0	.050	.080	1.01	5,000	C-2R
SML1240	12.0	.040	.088	1.11	5,000	C-2V
SML2450	24.0	.050	.279	3.51	5,000	C-2F
SML3020	30.0	.020	.104	1.31	5,000	C-2F

 THIRD ANGLE PROJECTION		METRIC DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		JKL COMPONENTS CORPORATION			
		DRAWN BY L. WENGSTROM		APPVD BY QC		DATE 8/16/00	
RELEASED		8/16/00		SIZE A		FSCM NO. 55335	
REV. NO.		DESCRIPTION/ECO NUMBER		APPVD DATE		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED	
TITLE T-1 1/4 TELEPHONE SLIDE BASE SPECIAL "L"		SCALE NONE		DRAWING NO. SLIDE BASE SPECIAL L T4.5L		RELEASED DATE 8/16/00	
REVISION DATE		REV. NO.		SHEET 1 OF 1			