




RECOMMENDED P.C.B. PATTERN LAYOUT

MATERIAL
 INSULATOR:PBT+30%G.F
 COLOR:BLACK/WHITE/BROWN/BEIGE-----
 CONTACT:BRASS
 SHELL:BRASS
 MECHANICAL
 MATING:35N MAX.
 WITHDRAWAL FORCE:10N MIN.
 DURAL LITY:1500 CYCLES MIN.
 ELECTRICAL
 CURENT-MAX[AMPS]:1.0A
 VOLTAGE-MAX[VOLTS]:30V
 WITHSTANDING VOLTAGE:100V AC.
 CONTACT RESISTANCE [OHMS]:50mΩ MAX.
 INSULATION RESISTANCE [OHMS]:1000MΩ MIN.
 PLATING
 CONTACT: GOLD PLATING CORD: 5u"
 SHELL:Nickel(Tin) OVER ALL PLATING
 ENVIRONMENTAL
 TEMPERATURE RANGE:-55°C to +85°C

RoHS
Compliant

ITEM NO AU-Y1008-R (Version 1.1, 5μ" Gold)
 AU-Y1008-2-R (Version 2.0, 30μ" Gold)

TITLE
 USB, Version A, 2 Port

ASSMANN
Electronics, Inc.

1840 W. Drake Drive, Suite 101 - Tempe, AZ 85283

Toll Free: 1-877-277-6266 Email: info@usa-assmann.com

THIS DRAWING IS UNPUBLISHED
 ©Copyright 2008 by Assmann Electronic Components
 All International Rights Reserved