

6.02191.50

BS 18 LTX Impuls

18 Volt Sordless drill/Screwdriver BS 18 LTX Impuls



4AH_0219100S_51.EPS

- Selectable "impuls" mode for removal of jammed screws and spot-drilling on smooth surfaces
- Extremely powerful thanks to powerful Metabo 4-pole motor for quick drilling and screwdriving
- Overload protection: protects the motor from overheating
- Spindle with hexagonal recess for screwdriver bits for working without chuck
- Neck (Ø 43 mm) for versatile use
- Integrated working light to illuminate the work site
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- With handy belt hook and bit holder, can be fixed either on the right or left side
- Battery packs with capacity display for checking the charge status
- Ultra-M technology for highest performance, gentle charging, optimum energy utilisation and long service life.
- 3-year battery pack warranty by means of Ultra-M technology

Comparative technical values

Type of battery pack	Li-ion
Battery pack voltage	18 V
Capacity of battery pack	4,0 Ah
Maximum torque, soft	55 Nm
Pulse torque	60 Nm
Maximum torque, hard	110 Nm
Adjustable torque	1,5 - 25 Nm
- Drill diameter in	
- Steel	13 mm
- Wood	65 mm
Idle revolutions	0 - 500 / 0 - 1.700 /min
Drill spindle thread	1/2 " - 20 UNF
Chuck adapter	1,5 - 13 mm
Weight (including battery pack)	2 kg

Scope of delivery

Futuro Plus quick-action keyless chuck with metal sleeve, Side handle, Belt hook with bit case, 2 Li-Power battery packs (18 V/4.0 Ah), Charger ASC 30-36 V "AIR COOLED", Plastic Carry Case