

Connector component - HC-B 16-TFQ-76/O1STM(32G-25G) - 1586002

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON B16 sleeve housing, for double locking latch, height: 76 mm, with 1 x M32/1 x M25 thread, straight cable outlet



Key commercial data

Packing unit	1 PCE
Minimum order quantity	10 PCE
Weight per Piece (excluding packing)	275.69 GRM
Custom tariff number	85369010
Country of origin	Germany

Technical data

Dimensions

Height	76 mm
Width	43 mm
Length	94 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-B16, BB32, D40, DD72, HS6, M, K
Design	B16
Housing type	Sleeve housings
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray

Connector component - HC-B 16-TFQ-76/O1STM(32G-25G) - 1586002

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM


ETIM 3.0	EC000437
ETIM 4.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Drawings

Dimensioned drawing



Connector component - HC-B 16-TFQ-76/O1STM(32G-25G) - 1586002

Dimensioned drawing

