



Wiha Hex Precision Series



263 Metric Hex Driver, With Precision Handle

Metric sizes. Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
263 07	0.7	.028	40	1.6	120	4.7	.02	10	
263 09	0.9	.035	40	1.6	120	4.7	.02	10	
263 13	1.27	.050	40	1.6	120	4.7	.02	10	
263 15	1.5	-	50	2.0	145	5.7	.03	10	
263 20	2.0	5/64	50	2.0	145	5.7	.03	10	
263 25	2.5	-	60	2.4	170	6.7	.04	10	
263 30	3.0	-	60	2.4	170	6.7	.04	10	
263 40	4.0	-	60	2.4	170	6.7	.05	10	

*Metric dimensions actual - Inch dimensions approximate



263 Inch Hex Driver, With Precision Handle

Inch sizes. Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	Inch	mm	mm	Inch	mm	Inch	lbs.	pkg.
263 07	.028	0.7	40	1.6	120	4.7	.02	10	
263 09	.035	0.9	40	1.6	120	4.7	.02	10	
263 13	.050	1.27	40	1.6	120	4.7	.02	10	
263 16	1/16	-	50	2.0	145	5.7	.03	10	
263 20	5/64	2.0	50	2.0	145	5.7	.03	10	
263 23	3/32	-	60	2.4	170	6.7	.04	10	
263 27	7/64	-	60	2.4	170	6.7	.04	10	
263 31	1/8	-	60	2.4	170	6.7	.04	10	
263 33	9/64	-	60	2.4	170	6.7	.05	10	
263 36	5/32	-	60	2.4	170	6.7	.05	10	

*Metric dimensions actual - Inch dimensions approximate



263 90 Set 7 Pcs. Hex Driver Metric

Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	mm	mm	lbs.
263 90	263 07	0.7	40	.28
	263 09	0.9	40	
	263 13	1.3	40	
	263 15	1.5	50	
	263 20	2.0	50	
	263 25	2.5	60	
	263 30	3.0	60	



263 91 Set 8 Pcs. Hex Driver Inch

Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	Inch	Inch	lbs.
263 91	263 07	.028	1.6	.32
	263 09	.035	1.6	
	263 13	.050	1.6	
	263 16	1/16	2.0	
	263 20	5/64	2.0	
	263 23	3/32	2.4	
	263 27	7/64	2.4	
	263 31	1/8	2.4	



911 18 Rugged Polyester Canvas Storage Pouch

Holds 8 Precision Tools up to 170mm in length. Folding pouch. Has security flaps and velcro closer.

Item	No.	Size	lbs.	pkg.
911 18	14 1/2" W x 7 3/4" L	.13	1	



263 99 Set 8 Pcs. Hex Inch In Canvas Pouch

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. In storage pouch

Item	No.	Inch	Inch	lbs.
263 99	263 07	.028	1.6	.55
	263 09	.035	1.6	
	263 13	.050	1.6	
	263 16	1/16	2.0	
	263 20	5/64	2.0	
	263 23	3/32	2.4	
	263 27	7/64	2.4	
	263 31	1/8	2.4	