

(1,00mm) .03937"

FJ SERIES

FJ-20-D-06.50-6

FJ-05-D-04.80-2

FLAT FLEXIBLE CABLE (FFC) JUMPER

SPECIFICATIONS

For complete specifications
see www.samtec.com/FJ

Conductor:

Tin Plated Copper

Conductor

Resistance:

300 Ω/km max

Insulation Resistance:

10 MΩ/km min

(conductor-to-conductor)

Dielectric Test:

400 VAC during 1 minute

(conductor-to-conductor)

Temperature Rating:

-30°C to +80°C

Voltage Rating:

300 VAC

Flame Resistance:

VW-1 (UL 758)

Current Rating:

1.9A @ 50°C ambient

(4 contacts powered)

RoHS Compliant:

Yes




Mates with:
FC1, ZF1

Double or
reversed ended

(1,00mm)
.03937"
pitch

Variable
lengths



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM