

Black & Gray Nylon Locking Nuts

Part Numbers		Thread Type & Size	Dimensions in Inches (mm)	
Black	Gray		G	H
			Thickness	Wrench Flats
NP-07-BK	NP-07-GY	PG 7	.20 (5)	.75 (19)
NP-09-BK	NP-09-GY	PG 9	.20 (5)	.87 (22)
NP-11-BK	NP-11-GY	PG 11	.20 (5)	.94 (24)
NP-13-BK	NP-13-GY	PG 13	.24 (6)	1.06 (27)
NP-16-BK	NP-16-GY	PG 16	.24 (6)	1.18 (30)
NP-21-BK	NP-21-GY	PG 21	.28 (7)	1.41 (36)
NP-29-BK	NP-29-GY	PG 29	.28 (7)	1.81 (46)
NP-36-BK	NP-36-GY	PG 36	.31 (8)	2.36 (60)
NP-42-BK	NP-42-GY	PG 42	.31 (8)	2.56 (65)
NP-48-BK	NP-48-GY	PG 48	.31 (8)	2.76 (70)
NN-09-BK	NN-09-GY	3/8" NPT	.28 (7)	.94 (24)
NN-13-BK	NN-13-GY	1/2" NPT	.24 (6)	1.06 (27)
NN-21-BK	NN-21-GY	3/4" NPT	.28 (7)	1.26 (32)
NN-29-BK	NN-29-GY	1" NPT	.28 (7)	1.57 (40)
NM-12-BK	NM-12-GY	M12 x 1.5	.20 (5)	.67 (17)
NM-16-BK	NM-16-GY	M16 x 1.5	.20 (5)	.87 (22)
NM-20-BK	NM-20-GY	M20 x 1.5	.24 (6)	1.06 (27)
NM-25-BK	NM-25-GY	M25 x 1.5	.28 (7)	1.42 (36)
NM-32-BK	NM-32-GY	M32 x 1.5	.28 (7)	1.61 (41)
NM-40-BK	NM-40-GY	M40 x 1.5	.28 (7)	1.97 (50)
NM-50-BK	NM-50-GY	M50 x 1.5	.31 (8)	2.36 (60)
NM-63-BK	NM-63-GY	M63 x 1.5	.31 (8)	2.95 (75)

EMI/RFI - Nickel Plated Brass Locking Nuts

Part Numbers	Thread Type & Size	Dimensions in Inches (mm)	
Nickel Plated Brass w/ Cutting Edges 		G	H
		Thickness	Wrench Flats
NP-07-BE	PG 7	.11 (2.8)	.59 (15)
NP-09-BE	PG 9	.11 (2.8)	.71 (18)
NP-11-BE	PG 11	.12 (3)	.83 (21)
NP-13-BE	PG 13	.12 (3)	.91 (23)
NP-16-BE	PG 16	.12 (3)	1.02 (26)
NP-21-BE	PG 21	.14 (3.5)	1.26 (32)
NP-29-BE	PG 29	.16 (4)	1.61 (41)
NP-36-BE	PG 36	.20 (5)	2.01 (51)
NP-42-BE	PG 42	.20 (5)	2.36 (60)
NP-48-BE	PG 48	.24 (6)	2.52 (64)
NN-13-BE	1/2" NPT	.13 (3)	.94 (24)
NM-12-BE	M12 x 1.5	.11 (2.8)	.59 (15)
NM-16-BE	M16 x 1.5	.11 (2.8)	.75 (19)
NM-20-BE	M20 x 1.5	.12 (3)	.94 (24)
NM-25-BE	M25 x 1.5	.14 (3.5)	1.18 (30)
NM-32-BE	M32 x 1.5	.20 (5)	1.42 (36)
NM-40-BE	M40 x 1.5	.20 (5)	1.81 (46)
NM-50-BE	M50 x 1.5	.20 (5)	2.36 (60)
NM-63-BE	M63 x 1.5	.24 (6)	2.76 (70)

Note: BE-Locknuts have the following approvals: CE & German Lloyd.

Nickel Plated Brass Locking Nuts


Part Numbers	Thread Type & Size	Dimensions in Inches (mm)	
Nickel Plated Brass 	See page 49 for thread specs	G	H
		Thickness	Wrench Flats
NP-07-BR	PG 7	.11 (2.8)	.59 (15)
NP-09-BR	PG 9	.11 (2.8)	.71 (18)
NP-11-BR	PG 11	.12 (3)	.83 (21)
NP-13-BR	PG 13	.12 (3)	.91 (23)
NP-16-BR	PG 16	.12 (3)	1.02 (26)
NP-21-BR	PG 21	.14 (3.5)	1.26 (32)
NP-29-BR	PG 29	.16 (4)	1.61 (41)
NP-36-BR	PG 36	.20 (5)	2.01 (51)
NP-42-BR	PG 42	.20 (5)	2.36 (60)
NP-48-BR	PG 48	.22 (5.5)	2.52 (64)
NN-09-BR	3/8" NPT	.14 (3.5)	.75 (19)
NN-13-BR	1/2" NPT	.12 (3)	.94 (24)
NN-21-BR	3/4" NPT	.14 (3.5)	1.18 (30)
NN-29-BR	1" NPT	.14 (3.5)	1.38 (35)
NM-06-BR	M6 x 1.0	.10 (2.5)	.39 (10)
NM-08-BR	M8 x 1.25	.10 (2.5)	.51 (13)
NM-10-BR	M10 x 1.5	.11 (2.8)	.51 (13)
NM-12-BR	M12 x 1.5	.11 (2.8)	.59 (15)
NM-16-BR	M16 x 1.5	.11 (2.8)	.75 (19)
NM-20-BR	M20 x 1.5	.12 (3)	.91 (23)
NM-25-BR	M25 x 1.5	.14 (3.5)	1.14 (29)
NM-32-BR	M32 x 1.5	.16 (4)	1.42 (36)
NM-40-BR	M40 x 1.5	.18 (4.5)	1.77 (45)
NM-50-BR	M50 x 1.5	.22 (5.5)	2.17 (55)
NM-63-BR	M63 x 1.5	.24 (6)	2.76 (70)

Zinc Plated Steel Locking Nuts


Part Numbers	Thread Type & Size	Dimensions in Inches (mm)	
	See page 49 for thread specs	G	H
		Thickness	Wrench Flats
NN-10-ST	1" NPT	.24 (6)	1.73 (44)
NN-34-ST	1-1/4" NPT	.20 (5)	2.01 (53)
NN-36-ST	1-1/2" NPT	.16 (4)	2.19 (55.5)




Nylon & Nickel Plated Brass Locknut



Zinc Plated Steel Locknut

**Stainless Steel (303)** Locking Nuts in PG & Metric threads are available upon request.See product information online. www.sealconusa.com

EMI/RFI Proof Locknut



For Material Specifications please refer to page 45.