

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1206150001](#)  
**Status:** **Active**  
**Overview:** Brad Ultra-Lock (M12) EX Connection System for Zone 2 Hazardous Locations  
**Description:** Ultra-Lock (M12) EX Receptacle, 3 Poles, 1/2 - 14 NPT, Female (Straight) to 22 AWG PVC Cable, 0.30m (11.81") Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837

**General**

Product Family Industrial Receptacles  
 Series [120615](#)  
 IP Rating IP69K  
 NEMA Rating NEMA 6  
 Overview [Brad Ultra-Lock \(M12\) EX Connection System for Zone 2 Hazardous Locations](#)  
 Product Name Ultra-Lock (M12) EX  
 Type Single Ended (pigtail)  
 UPC 78172535790

**Physical**

Coupling Type Internal Thread  
 Gender Female  
 Keyway Single  
 Length 0.30m  
 Material - Component Nickel-plated Brass  
 Mounting Thread Size 1/2" - 14 NPT  
 Orientation Straight  
 Panel Mount Front  
 Poles 3  
 Temperature Range - Operating -20°C to +80°C  
 Wire Size AWG 22  
 Wire/Cable Type UL 1061

**Electrical**

Current - Maximum per Contact 4.0A  
 Voltage - Maximum 125V

**Material Info**

Engineering Number LWR3000A18C300

**Reference - Drawing Numbers**

Sales Drawing SD-120614-999, SD-120615-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[120615 Series](#)