



Innovative **Technology**
for a **Connected** World

Tflex™ SF200 Series

Thermal Gap Filler

Preliminary



LOW CONTACT RESISTANCE SILICONE-FREE GAP FILLER

Tflex™ SF200 is a compliant, silicone free, thermal interface material featuring extremely low contact resistance for effective heat transfer. While Tflex™ SF200 is exceptionally suited for silicone sensitive applications, its ease of handling and exceptional wetting properties make it an effective solution in applications where silicone pads are traditionally used.

Tflex™ SF200 is naturally tacky on both sides requiring no additional adhesive coating, which would inhibit thermal performance. The natural tack allows for the pad to be held in place during assembly. Differential tack is available for easy assembly and rework.

FEATURES AND BENEFITS

- Silicone-free gap pad
- Low contact resistance for effective thermal transfer
- Easy to handle in all thicknesses
- Thermal Conductivity for material thicknesses of 10 to 30 mils is 1.8 W/mK
- Thermal Conductivity for material thicknesses of 40 to 140 mils is 2.0 W/mK
- Available in thicknesses from 0.010-inch (0.25 mm) through 0.140-inch (3.56 mm) in 0.010-inch increments

APPLICATIONS

- Silicone-sensitive applications
- Automotive applications
- Optical components
- Flat panel displays
- Hard disk drives
- Medical devices
- Laser equipment
- Aerospace electronics
- Solar energy

global solutions: local support™

Americas: +1.800.843.4556

Europe: +49.8031.2460.0

Asia: +86.755.2714.1166

CLV-customerservice@lairdtech.com


www.lairdtech.com/thermal


Tflex™ SF200 TYPICAL PROPERTIES

	Tflex™ SF200 10 - 30 mils	Tflex™ SF200 40 - 140 mils	TEST METHOD
Construction	Unreinforced, Ceramic filled pad		
Color	Rose	Rose	Visual
Thermal Conductivity (W/mK)	1.8	2.0	Hot Disk
Thickness Range (inches/mm)	0.010 - 0.030 / 0.25 - 0.75	0.040 - 0.140 / 1.00 - 3.56	
Thickness Tolerance (%)	± 10	± 10	
Density (g/cc)	2.8	2.8	Helium Pycnometer
Hardness (Shore 00)	73; 3 seconds 70; 30 seconds	68; 3 seconds 65; 30 seconds	ASTM D2240
Volatile Siloxane (D3-D10)	none detected*	none detected*	GC/MS in hexane
UL Flammability Rating (UL 94)	V0**	V0**	File E180840
Continuous Use Temperature (°C)	-20 to 120	-20 to 120	TGA
CTE (ppm/°C)	226.3; 25°C to 80°C 913.6; 80°C to 120°C	226.3; 25°C to 80°C 913.6; 80°C to 120°C	IPC-TM-650 2.4.24
Heat Capacity at 50°C (J/g-K)	0.79	0.79	ASTM E1269
Volume Resistivity, ohm-cm	10 ¹⁴	10 ¹⁴	ASTM D257
Dielectric Constant	4.8 at 1kHz 1.7 at 1MHz	5.8 at 1kHz 3.9 at 1MHz	ASTM D150
Bellcore (Telcordia) Silicone Extraction	Pass	Pass	TR-NWT-000930
Weight Loss at 120°C for 168 hrs (%)	<0.2	<0.2	TGA

* Method detection limit = 40 ppm

** pending





STANDARD THICKNESSES

Standard thickness is 0.010-inch (0.25 mm) through 0.140-inch (3.56 mm) in 0.010-inch increments.

OPTIONS

Material is standard with both sides tacky; the -DF suffix indicates differential tack (one side not tacky).

MATERIAL NAME AND THICKNESS

Tflex™ indicates Laird Technologies' gap filler product line. SF2XXX indicates Tflex SF200 product line with thickness in mils (0.001-inches)

EXAMPLES

Tflex™ SF240 = standard 0.040-inch thick Tflex™ SF200 material

Tflex™ SF2100 = standard 0.100-inch thick Tflex™ SF200 material

Tflex™ SF260 DF = standard 0.060-inch thick material with DF

Data for design engineer guidance only. Observed performance varies in application.

Engineers are reminded to test the material in application.

THR-DS-Tflex-SF200 1112

Any information furnished by Laird Technologies, Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Technologies materials rests with the end user. Laird Technologies makes no warranties as to the fitness, merchantability, suitability or non-infringement of any Laird Technologies materials or products for any specific or general uses. Laird Technologies shall not be liable for incidental or consequential damages of any kind. All Laird Technologies products are sold pursuant to the Laird Technologies' Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2012 Laird Technologies, Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Technologies Logo, and other marks are trademarks or registered trademarks of Laird Technologies, Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird Technologies or any third party intellectual property rights. Document A16814-00 Rev A, 10/30/12.