







716 6321

walthers

Amp	Volt	Hz	IP Ident. colour + h	Part No	Couplers	2 P +	 9	EAN No. 4015609...																														
					<table><tr><th>Ampère</th><th>d</th><th>e</th><th>f</th><th>p</th></tr><tr><td>16 A</td><td>95</td><td>50,3</td><td>80</td><td>8/13</td></tr></table>	Ampère	d	e	f	p	16 A	95	50,3	80	8/13																							
Ampère	d	e	f	p																																		
16 A	95	50,3	80	8/13																																		
					<table><tr><th>Ampère</th><th>a</th><th>d</th><th>e</th><th>f</th><th>Øp</th></tr><tr><td>16 A</td><td>54</td><td>87</td><td>49,5</td><td>140</td><td>7/13</td></tr></table>	Ampère	a	d	e	f	Øp	16 A	54	87	49,5	140	7/13																					
Ampère	a	d	e	f	Øp																																	
16 A	54	87	49,5	140	7/13																																	
					<table><tr><th>Ampère</th><th>d</th><th>f</th><th>m</th><th>u</th><th>Pg</th></tr><tr><td>16 A</td><td>136</td><td>78</td><td>121</td><td>72</td><td>13,5</td></tr><tr><td>32 A</td><td>170</td><td>96</td><td>149</td><td>96</td><td>21</td></tr><tr><td>63 A</td><td>255</td><td>117</td><td>206</td><td>110</td><td>36</td></tr><tr><td>125 A</td><td>332</td><td>130</td><td>275</td><td>130</td><td>48</td></tr></table>	Ampère	d	f	m	u	Pg	16 A	136	78	121	72	13,5	32 A	170	96	149	96	21	63 A	255	117	206	110	36	125 A	332	130	275	130	48			
Ampère	d	f	m	u	Pg																																	
16 A	136	78	121	72	13,5																																	
32 A	170	96	149	96	21																																	
63 A	255	117	206	110	36																																	
125 A	332	130	275	130	48																																	

			IP		Wall socket outlets with switch		2 P + 		 9	EAN No. 4015609...
Amp	Volt	Hz	Ident. colour + h	Part No.			IEC/EN 60 309			
					with double interlocking, switch 2 poles				1 796	039562 039555 039579
IP44										
16	230	50/60	6	531 23 16					1 1039	039609 039593 039616
	110	50/60	4	531 23 14						
	400	50/60	9	531 23 19						
32	230	50/60	6	531 23 36					1 1039	039609 039593 039616
	110	50/60	4	531 23 34						
	400	50/60	9	531 23 39						
					with double interlocking, switch 2 poles				1 2482	039630 039623 039647
IP44										
63	230	50/60	6	531 23 66					1 2482	039630 039623 039647
	110	50/60	4	531 23 64						
	400	50/60	9	531 23 69						
					with double interlocking, switch 2 poles				1 845	039944 133116 166251
IP67										
16	230	50/60	6	531 33 16					1 1066	134267 166268 166275
	110	50/60	4	531 33 14						
	400	50/60	9	531 33 19						
32	230	50/60	6	531 33 36					1 1066	134267 166268 166275
	110	50/60	4	531 33 34						
	400	50/60	9	531 33 39						
					with double interlocking, switch 2 poles				1 2533	174034 039951 166282
IP67										
63	230	50/60	6	531 33 66					1 2533	174034 039951 166282
	110	50/60	4	531 33 64						
	400	50/60	9	531 33 69						