


Crimphousing 1,25 mm

Series

425




Rated current	1,0 A
Rated voltage	100 V _{RMS} / V _{DC}
Withstand voltage	500 V _{RMS} for 1 minute
Material contact	Copper alloy
Material insulator	Thermoplast UL94V-0
Operating temperature	-40°C to +105°C

pitch
1,25

max.
pincount
015

All dimensions in mm.

Variation




1

Contact

Series

606

AWG 28 - 32



Plating:
T = Sn

Packaging:
R = Reel


Plating contact

Packaging

6	0	6	-	1	-	T	X	-	X	R
---	---	---	---	---	---	---	---	---	---	---

Crimp Tool

454



no. of contacts		
n	A	B
002	4,25	1,25
003	5,50	2,50
004	6,75	3,75
005	8,00	5,00
006	9,25	6,25
007	10,50	7,50
008	11,75	8,75
009	13,00	10,00
010	14,25	11,25
011	15,50	12,50
012	16,75	13,75
013	18,00	15,00
014	19,25	16,25
015	20,50	17,50

4	5	4	-	1	-	0	1
---	---	---	---	---	---	---	---

Variation

No. of contacts



GARRY

www.mpe-connector.de

0000000000

Order code:

4 2 5 - 1 - ? ? ? - X - K S 0

Mating series	426	427
see page	3-10	3-11