


## UNSHIELDED PLASTIC or TPE JACKETED MINIATURE CORDS UL LISTED



Stranded tinned copper,  
polypropylene insulated,  
black PVC jacketed.  
Temperature Rating: -20C + 80C

| OLYMPIC NO.                         | AVAIL. LENGTHS (RETRACTED) (INCHES) | NO. OF COND. | AWG NO. | MAX WORKING VOLTAGE | STRAND NO./AWG | COND. AMP RATING | CABLE O.D. (INCHES) | COIL O.D. (INCHES) |
|-------------------------------------|-------------------------------------|--------------|---------|---------------------|----------------|------------------|---------------------|--------------------|
| 6516P                               | 48,36,24,12                         | 2            | 28      | 300                 | 7/36           | 1/2              | .140                | 1/2                |
| 6517P                               | 48,36,24,12                         | 3            | 28      | 120                 | 7/36           | 1/2              | .150                | 1/2                |
| 6518P                               | 48,36,24,12                         | 4            | 28      | 120                 | 7/36           | 1/2              | .155                | 1/2                |
| 6519P                               | 48,36,24,12                         | 5            | 28      | 120                 | 7/36           | 1/2              | .165                | 9/16               |
| 6520P                               | 48,36,24,12                         | 6            | 28      | 120                 | 7/36           | 1/2              | .180                | 5/8                |
| 6521P                               | 48,36,24,12                         | 7            | 28      | 120                 | 7/36           | 1/2              | .180                | 5/8                |
| 6522P                               | 48,36,24,12                         | 8            | 28      | 120                 | 7/36           | 1/2              | .195                | 5/8                |
| RETRACTED - EXTENDED RATIO (1 TO 5) |                                     |              |         |                     |                |                  |                     |                    |
| 48" - 20'                           |                                     | 36" - 15'    |         | 24" - 10'           |                | 12" - 5'         |                     |                    |
| STRAIGHT LEAD LENGTHS               |                                     |              |         |                     |                |                  |                     |                    |
| 6"                                  |                                     | 6"           |         | 6"                  |                | 12"              |                     |                    |

## UNSHIELDED PLASTIC or TPR JACKETED COMMUNICATIONS & ELECTRONIC CONTROL CORDS



**UL LISTED**  
Stranded tinned copper,  
polypropylene insulated,  
PVC or TPR jacketed.  
Temperature Rating: -20C + 80C

| OLYMPIC NO.         | AVAIL. LENGTHS (RETRACTED) (INCHES) | NO. OF COND. | AWG NO. | MAX WORKING VOLTAGE | NOM. AREA (mm) | STRAND NO./AWG | COND. AMP RATING | CABLE O.D. (INCHES) | COIL O.D. (INCHES) |
|---------------------|-------------------------------------|--------------|---------|---------------------|----------------|----------------|------------------|---------------------|--------------------|
| * 6370P<br>** 6382P | 48,36,24,12                         | 2            | 23      | 300                 | .259           | 21/36          | 1                | .180                | 5/8                |
| * 6371P<br>** 6383P | 48,36,24,12                         | 3            | 23      | 120                 | .259           | 21/36          | 1                | .190                | 11/16              |
| * 6372P<br>** 6384P | 48,36,24,12                         | 4            | 23      | 120                 | .259           | 21/36          | 1                | .200                | 11/16              |
| * 6373P<br>** 6385P | 48,36,24,12                         | 5            | 23      | 120                 | .259           | 21/36          | 1                | .215                | 3/4                |
| * 6374P<br>** 6386P | 48,36,24,12                         | 6            | 23      | 120                 | .259           | 21/36          | 1                | .230                | 7/8                |
| * 6375P<br>** 6387P | 48,36,24,12                         | 7            | 23      | 120                 | .259           | 21/36          | 1                | .230                | 7/8                |
| * 6376P<br>** 6388P | 48,36,24,12                         | 8            | 23      | 120                 | .259           | 21/36          | 1                | .245                | 7/8                |
| * 6377P<br>** 6389P | 48,36,24,12                         | 10           | 23      | 120                 | .259           | 21/36          | 1                | .280                | 15/16              |
| * 6378P<br>** 6390P | 48,36,24,12                         | 12           | 23      | 120                 | .259           | 21/36          | 1                | .285                | 1                  |
| * 6379P<br>** 6391P | 48,36,24,12                         | 15           | 23      | 120                 | .259           | 21/36          | 1                | .310                | 11/16              |

\* Black PVC jacket  
\*\* Black TPR jacket