


ED555/XDS



2-16 poles, Spacing 3.5 mm

insert required no. of poles **X**

How to order see page 5



Ratings:

Rated Voltage

150 V

130 V

Rated Current

6 A

13.5 A (T60)

Wire Size

AWG 28-16

1.0 mm²

Test Voltage

2.0 kV

Rated Torque/ScrewSize

0.4 Nm/M2

Max. Rated Cross Section

Single Wire (solid)

1.5 mm²

Stranded Wire (flexible)

1.5 mm²

Stranded wire with Ferrules

0.75 mm²

Dimensions

Spacing

3.5 mm

PCB Hole Diameter

1.2 mm

Stripped Length

5.5 mm

Materials

Insulating Material

PA

Flammability Class

UL94 V-0

Temperature Range

-30°C/+105°C

Terminal Block


CuZn

Wire Guard

Stainless Steel

Color

Grey



P = No. of poles