




1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X $\pm$ 0.4
X.XX $\pm$ 0.25
3. TERMINAL NUMBERS FOR REF. ONLY
4. CONTACT RATING: 0.1A @ 30VDC
5. CONTACT RESISTANCE: 50m OHM MAX.
- ▲ 6. TRAVEL: FULL = 2.5 $\pm$ 0.3
7. OPERATING FORCE: 250 $\pm$ 100gf
8. ELECTRICAL LIFE: 10,000 CYCLES
9. ▲ DENOTES CRITICAL PARAMETER
10. CONTACT MATERIAL: SILVER
11. OPERATING TEMPERATURE: -20c TO +70c
12. INSULATION RESISTANCE: 100M OHMS
- ▲ 13. LED COLOR: GREEN
14. 2002/95/EC (RoHS) COMPLIANT AND HALOGEN FREE



7. OPERATING FORCE: 250± 100gF
8. ELECTRICAL LIFE: 10,000 CYCLES
9. ▲ DENOTES CRITICAL PARAMETER
10. CONTACT MATERIAL: SILVER
11. OPERATING TEMPERATURE: -20c TO +70c
12. INSULATION RESISTANCE: 100M OHMS MIN.
▲ 13. LED COLOR: GREEN



B	19334	DIJIM CHANGES & UPDATES	12/30/10	BGL
A	18806	New-Release	1/20/10	rc
TITLE TL22050ABPGA				

REV	PCK NO	DESCRIPTION	DATE	BY
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				
		SCALE	2	
		DATE	1/20/2010	
		DR	rc	
		DWG	B401005	
		REV	B	