




A Phoenix Mecano Company



From: Sales [Sales@apem.co.uk]

Sent: 01 December 2006 12:20

Subject: PK20 03 or AK100 Series.pdf

Attachments: PK20 03 or AK100 Series.pdf

Page 1 of 1

01/12/2006

AK100/..DS-10.0-V-GREY

2-12 poles, spacing 10,0 mm

Insert required no. of poles ..

Ratings:

		
Rated Voltage	300 V	750 V
Rated Current	15 A	24 A (T60)
Wire Size	AWG 22-14	2,5 mm ²
Test Voltage		3,5 kV
Rated Torque / Screw Size		0,5 Nm / M3

Max. Rated Cross Section

Single Wire (solid)	2,5 mm ²
Stranded Wire (flexible)	1,5 mm ²
Stranded Wire with Ferrules	1,5 mm ²

Dimensions

Spacing	10 mm
PCB hole diameter	1,3 mm
Stripped Length	7 mm

Materials

Insulating Material	PA
Flammability Class	UL94 V-0
Temperature Range	-30°C/105°C
Terminal Block	CuZn
Wire guard	stainless steel

Colour

GREY	RAL 7016
------	----------

