

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.


© COPYRIGHT — By —

LOC
DWDIST
/






REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B5	REVISED (ECR-15-000347)	16DEC14	S.H	V.P

- EU ROHS-RELATED RESTRICTED SUBSTANCE SPEC IN HOMOGENEOUS MATERIAL REFER TO TEC-138-702 REV.G:
LEAD < 1000PPM, CADMIUM < 100PPM, MERCURY < 1000PPM
CHROMIUM VI < 1000PPM, PBB <1000PPM, PBDE < 1000PPM
- HALOGEN FREE SPEC:
CHLORINE (Cl): 900 ppm MAX.
BROMINE (Br): 900 ppm MAX.
CHLORINE (Cl) + BROMINE (Br): 1500 ppm MAX.



A-A



A'SSY P/N					
	2-2129345-1	1-2129345-2	1-2129345-1	2129345-2	2129345-1
DIM B	1.2	1.2	1.4	1.2	1.4
DIM A	1.2	1.2	1.4	1.2	1.4


1	1	1	1	1	0.002mm MATTE TIN PLATING ON SOLDER AREA, 0.00127mm MIN. NICKEL UNDERPLATED ALL OVER	COPPER ALLOY	GROUND SHELL	⑤
2	2	2	2	2	0.0002mm GOLD PLATING ON CONTACT AREA, 0.002mm MATTE TIN PLATING ON SOLDER AREA, 0.002mm MIN. NICKEL UNDERPLATED ALL OVER	COPPER ALLOY	POWER CONTACT	④
1	1	1	1	1	0.0002mm GOLD PLATING ON CONTACT AREA, 0.002mm MATTE TIN PLATING ON SOLDER AREA, 0.002mm MIN. NICKEL UNDERPLATED ALL OVER	COPPER ALLOY	DETECT CONTACT	③
2	2	2	2	2	0.0002mm GOLD PLATING ON CONTACT AREA, 0.002mm MATTE TIN PLATING ON SOLDER AREA, 0.002mm MIN. NICKEL UNDERPLATED ALL OVER	COPPER ALLOY	GROUND CONTACT	②
1	/	/	/	/	BLACK	HIGH TEMPERATURE THERMO-PLASTIC (UL94V-0)	HOUSING	①
/	1	1	1	1	YELLOW			
Q'TY					FINISH/COLOR	MATERIAL	PART NAME	NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH
	±0.25 ±3° ±
MATERIAL SEE TABLE	

DWN S.HUANG	24FEB12
CHK V.PENG	24FEB12
APVD W.KODAMA	24FEB12
PRODUCT SPEC	
108-99035	
APPLICATION SPEC	
501-99040	
WEIGHT	
CUSTOMER DRAWING	

TE Connectivity			
NAME DC POWER JACK CONNECTOR DIP TYPE			
SIZE A3	CAGE CODE 00779	DRAWING NO C-2129345	RESTRICTED TO /
SCALE 4:1		SHEET 1 OF 3	REV B5



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — By —

LOC
DW

	DIST
	

REVISIONS

	F
--	---

LTR

DESCRIPTION






DATE _____

DWN

APVD

SEE SHEET 1

4. SHIPPING BOX DIMENSION: 445mmX445mmX270mm



450	5	2250
PCS/REEL	REEL/SHIPPING BOX	TOTAL Q'TY



TE Connectivity

NAME	DC POWER JACK CONNECTOR
	DIP TYPE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2129345	—

CUSTOMER DRAWING	SCALE	NA	SHEET	3 OF 3	REV	B5
------------------	-------	----	-------	--------	-----	----

THIS DRAWING IS A CONTROLLED DOCUMENT

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0	PLC	$\pm -$	$\pm 0.$ $\pm 3^\circ$
1	PLC	$\pm -$	
2	PLC	$\pm -$	
3	PLC	$\pm -$	
4	PLC	$\pm -$	
ANGLES		$\pm -$	
FINISH			

[illegible]

	DW
--	----

CH

AD

PRODUCT SPEC

23	APPLICATION SPEC
----	------------------

WEIGHT

CUSTOMER DRAWING