

MICRO SWITCH
a Honeywell Division

FED MFG CODE 91929

ASSEMBLY - PUSHBUTTON SWITCH

CATALOG LISTING
1PB591

CATALOG LISTING
1PB591
PAGE 1 OF 1

M

DRAWING
NUMBER

3

ISSUE

RELEASE NO. PR-18773-T REPLACES X92458-PB

CHECK

REVISIONS
A 201261
7 SEP 00
B 0018501
TSG
20 FEB 06

RJ

CHECK

27 NOV '90


DAW

CHECK

DCS 26 NOV 90

RASTER

DRAWN




NOTES

- 1 - UNIT INCLUDES "11SM" BASIC SWITCH
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - RECOMMENDED FOR MANUAL OPERATION ONLY
- 4 - FOR USE IN TEMPERATURE RANGE -65°F TO $+400^{\circ}\text{F}$
- (5) MOUNTING HARDWARE FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE - - - - 2 LBS MAX
OVERTRAVEL FORCE - - - - 2.5 LBS MAX
RELEASE FORCE - - - - -2 OZ MIN

DIFFERENTIAL TRAVEL - - - - .031 MAX
OVERTRAVEL - - - - - .100 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

250 VAC - - - - - 5 AMP

30 VOLTS DC RATING

INDUCTIVE - - - - SEA LEVEL - - 3 AMP
50,000 FT - 25 AMP
RESISTIVE - - - - SEA LEVEL - 5 AMP
50,000 FT - 5 AMP
MAXIMUM INRUSH - - - - - 24 AMP

SCALE FULL

DO NOT
SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.) $\pm .030$

TWO PLACE (.00) $\pm .015$

THREE PLACE (.000) $\pm .005$

ANGLES $\pm$

WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1PB591](#)