Pomona®

Model B
Stack-Up Banana Plug
Both Ends



FEATURES:

- Mates to Model #1581, 2854 or standard Banana Jack.
- Cross and vertical stacking banana plug.
- Ideal for providing jumpers or chassis boxes.

MATERIALS:

Conn: Extension Stacking Banana Plug

Material: Spring, Beryllium Copper per QQ-C-533, Allow 172, Cond. HT.
Plug Body: Brass, per QQ-B-626, Alloy 360, ½ hard.
Finish: Nickel plate per QQ-N-290 class 2, 200/300 microinches.
Insulation: Polypropylene molded to plug body and wire
Color: Matches color of wire.
Marking: "MODEL B-XX"
Wire: 18 AWG, stranding 65 x 36 t.c., PVC insulated, 3.66 (.144) O.D.
Color: See Ordering Information
Marking: "POMONA B-XX-*"

RATINGS: (Entire Assembly)

Operating Temperature.: +55ºC. (+131ºF.) Max.
Operating Voltage: Hand-held Testing: 30VAC/60 VDC Max.
Hands free testing in Controlled Voltage Environment: 5000 WVDC
Current: 15 Amperes Cont.

ORDERING INFORMATION: Model B-XX-*

XX = Cable Lengths, Standard Lengths: 4" (102), 8" (203), 12" (305), 18" (457), 24" (610), 36" (914), 48" (1219), 60" (1524) & 72" ((1829). Additional lengths can be quoted upon request.

*= Color, -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White

Ordering Example: B-72-2 Indicates 72" in length, Color is Red.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (,51 mm), .xxx = ± .005" (,127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

Pomona*ACCESS* **90534** (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com