





LOC	DIST	REVISIONS			
		LTR	DESCRIPTION	DATE	APVD
H	-	E1	REVISED PER ECO-11-005294	30APR11	HMR



- NOTES:
- 1. WIRE RANGE 24-20 AWG
 - 2. INSULATION RANGE Ø .50- .060 (1,27-1,52 mm)
 - 3. FOR APPLICATOR USE ONLY
 - 4. FOR HANDTOOL USE ONLY
 - 5. FOR APPLICABLE CONNECTOR HOUSINGS SEE C-338095.



4	750	Pre-Tin	COSI-contact	Phosphorbronze	1-0338097-1
3	15000	Pre-Tin	COSI-contact	Phosphorbronze	0-0338097-1
	Pcs/reel	Finish	Description	Material	Partnumber
DWN M.V.AMELSFORT					
CHK Hv.Delft					
APVD -					
PRODUCT SPEC 108-19052					
APPLICATION SPEC 114-19051					
WEIGHT -					
CUSTOMER DRAWING					
TE Connectivity					
NAME MICRO-MATCH COSI CONTACT					
20-24 AWG					
SIZE A3					
CAGE CODE 00779					
DRAWING NO C- 338097					
SCALE 10:1					
SHEET 1 OF 1					
REV E1					

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
	0 PLC	±	0,2
	1 PLC	±	0,1
	2 PLC	±	0,05
	3 PLC	±	0,01
	4 PLC	±	-
	ANGLES	±	0,2°
MATERIAL		FINISH	
		Pre-tinplated	