

Pin Header Shrouded 1,25 mm

Series

426

pitch

1,25

termination

max.
pincount


015

Rated current	1,0 A
Rated voltage	100 V _{RMS} / V _{DC}
Withstand voltage	300 V _{RMS} for one minute
Material contact	Copper alloy
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +105°C
Max. processing temper.	260°C for 10 seconds



All dimensions in mm.

Variation


PCB Layout



1



2



no. of contacts	see figure left	see figure left	available in variation	
n	A	B		
002	4,25	1,25	1	2
003	5,50	2,50	1	2
004	6,75	3,75	1	2
005	8,00	5,00	1	2
006	9,25	6,25	1	2
007	10,50	7,50	1	2
008	11,75	8,75	1	2
009	13,00	10,00	1	2
010	14,25	11,25	1	2
011	15,50	12,50	1	2
012	16,75	13,75	1	2
013	18,00	15,00	1	2
014	19,25	16,25	1	2
015	20,50	17,50	1	2

Plating:
T = Sn

Variation (1,2)

No. of contacts

Plating contact



www.mpe-connector.de

Order code:

426-2-222-0-T-KS0

Mating series
see page425
6-3