






POS sockets in 7,62mm/.300" DIP spacing are either supplied with or without bars in the centre depending on plastic wafer availability. If you need sockets without centre bars, then please always order with POO instead of POS.

Pin	Dimension		Available Pinouts of Series		
	"A"	"B"	POS	POO	PCL
10	12,60	5,08 .200"	-210-	-210-	-210-
6	7,60	7,62 .300"	-306-	-	-
8	10,10		-308-	-	-308-
10	12,60		-310-	-	-
14	17,70		-314-	-	-314-
16	20,30		-316-	-	-316-
18	22,80	7,62 .300"	-318-	-318-	-318-
20	25,30		-320-	-320-	-320-
22	27,80		-322-	-322-	-
24	30,40		-324-	-324-	-
28	35,50		-328-	-328-	-
16	20,32	10,16 .400"	-416-	-416-	-416-
22	27,80		-422-	-422-	-422-
24	30,60		-424-	-424-	-424-
24	30,50	15,24 .600"	-624-	-624-	-624-
28	35,50		-628-	-628-	-628-
32	40,60		-632-	-632-	-632-
36	45,70		-636-	-636-	-
40	50,80		-640-	-640-	-640-
48	60,96		-648-	-648-	-648-
64	81,26	22,86 .900"	-964-	-964-	-



Specifications

see page 71
of this catalogue.

Insulator body

POS series = open insulator - see drawings above
 POO series = open insulator w/o centre bars
 PCL series = closed insulator body

Terminals


The **POS, POO** and **PCL** series are available with many different terminal styles. The most common terminal styles are shown on the right hand side of this page. Many other additional terminals can be found at the end of this catalogue. Custom design terminals are available on request.

How to order

XXX - x xx - S xxx - xx

Series POS POO PCL	DIP spacing (inch) see above table, dimension "B" Example: 3 for .300" ----- insert the corresponding data of the POS, POO or PCL column	Nbr of contacts see above table Example: 06 for 6 Pin ----- insert the corresponding data of the POS, POO or PCL column	Terminal style see drawings above or refer to last pages of this catalogue for other types.	Plating - 95 = tin/gold - 55 = gold/gold - 99 = tin/tin (tin leadfree)
---	--	---	---	--

Board to Board Terminals



Header Terminals

