

CABLE-D25SUB/S/S/200/KONFEK/S

Order No.: 2305648

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2305648>

Assembled, shielded circular cable, with D-SUB pin strip, 25-pos. from both sides, cable length: 2m

Commercial data

EAN	4046356011983
Pack	1 pcs.
Customs tariff	85444290
Weight/Piece	0.3757 KG
Catalog page information	Page 271 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
01/10/2007



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General**

Nominal voltage U_N	125 V AC/DC
Max. current carrying capacity per path	2 A
Max. conductor resistance	$\leq 0.09 \Omega/m$
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Number of positions	25
Number of positions, control side	25
Number of connectors, control side	1
Number of positions, module side	25
Number of connectors, modul side	1
Fixed cable length	2 m
Single wire, cross section	0.25 mm ²
AWG	24
External diameter	10.5 mm
Shielding	yes
	Tinned copper-braided shield, approx. 85% covering
Insertion/withdrawal cycles	> 200
Width	53 mm
Length	40 mm

Certificates / Approvals



Certification

CUL, UL

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;