


HONEYWELL PART NUMBER
192-303KET-A02


REV	DOCUMENT	CHANGED BY	CHECK
B	0039479	SS 05MAY08	BLR



CHIP	091-303KET-001
DIAMETER	.075 MAX
LEAD LENGTH	1 1/2 MIN
LEAD	900-032U1A-BBP WIRE 32 AWG TIN COATED COPPER ALLOY 180
SOLDER	900-740S17-A01 TIN 96% SILVER 4%
FLUX	ORGANIC, WATER SOLUBLE
COATING	908-5EPMIX-A60 (BLACK EPOXY)
AGE	5 DAYS AT 105°C, 5 DAYS AT 50°C

RESISTANCE	TEMP. (°C)	MINIMUM (OHMS)	NOMINAL (OHMS)	MAXIMUM (OHMS)	REF. TOL
	70	5312.9	5349	5385.4	±0.2°C
	0	94,545	95,490	96,445	±0.2°C

NOTE:
1. RoHS COMPLIANT

DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: FRACTIONS X ± 1/64 ONE PLACE .X ± - TWO PLACE .XX ± 0.01 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± - ANGLES X ± 0°30'	DRAWN	HW	27OCT00	Honeywell			
	CHECK	JF	27OCT00				
	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE THERMISTOR OUTLINE			
	INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY						
	THIRD ANGLE PROJECTION 			SIZE B	TYPE I	DRAWING NAME 192-303KET-A02	
AUTO CAD 2D			SCALE -		SHEET		1 OF 1