






Dimensions: mm (in.)**P.C. Mounting**

POS.1	POS.2
ON	(ON)
2-3	2-1

Switch Function**Mechanical Specifications:**

- Mechanical Life: 50,000 make-and-break cycles
- Operating Temperature: -30°C to 85°C

Electrical Specifications:

- Rating: 0.4VA Max./20V AC or DC Max.
- Contact Resistance: 20mΩ max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩ min.
- Dielectric Strength: 1,000 V RMS@sea level

Note:

- RoHS Compliant by exemption

Solder Process:

- Wave soldering: Recommended soldering temperature: 260±5°C
Duration of solder immersion: 5±1 seconds (PCB is 1.6mm in thickness)

Sealed Sub-Miniature Toggle Switch
108-2BS2T2Z50-EVX

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[108-2BS2T2Z50-EVX](#)