







# Modular Jack Plate

154-3008

KOBI CONN

Modular Jack Plate



Dimensions: In.

SPECIFICATIONS	
Type:	Surface Mount 6P/6C
Contact Resistance:	30mΩ max.
Current Rating:	1.5A max.
Withstand Voltage:	500VAC for 1 Minute
Cover:	ABS
Contacts:	6μ Gold over 100μ Nickel Plated Phosphor Bronze
Lead Wires:	26AWG
Y-Terminal:	Copper
Screws:	Nickel Plated, Self-Tapping

Date Last Revised: 11-3-05

154-3008

Available from Mouser Electronics  
1-800-346-6873  
[www.mouser.com](http://www.mouser.com)

KC-300653

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-3008](#)