

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

09-93-1500

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 3.96mm Crimp Terminal Housing, Friction Ramp, 15 Circuits, Glow Wire Compatible

Documents:

3D Model

Drawing (PDF)

Product Specification PS-99020-0087 (PDF)

Packaging Specification PK-3069-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Comments

Crimp Housings

3069

Power, Wire-to-Board

This Molex product is manufactured from material that has the following ratings, tested by independent agencies :. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety; section 30 Resistance to heat and fire.<P><P>The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s).<P>If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.

KK® Interconnect System - Molex

KK® 396

883906174309

Overview

Product Name

UPC

KK® Interconnect System - Molex

KK® 396

883906174309

Physical

Circuits (maximum)

Circuits Detail

Color - Resin

Gender

Glow-Wire Compliant

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Temperature Range - Operating

15

15

Black

Female

Yes

Yes

Nylon

3.786/g

1

Bag

No

3.96mm

See Product Specification

Material Info

Old Part Number

3069-G15

Reference - Drawing Numbers



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

3069Series

Mates With

2220 , 3190 , 3192 , 3243, 3246, A4042, 41661 , 41662 , 41671 , 41672 , 41681 , 41682 , 41701 , 41711 , 41721 , 41741 , 41761 , 41771 , 41772 , 41791 , 41792 , 42441 , 42461 , 42471 , 42491

Use With

2478 Crimp Terminals for 18-24 AWG, 2578 Crimp Terminals for 22-26 AWG

Packaging Specification
Product Specification
Sales Drawing

PK-3069-001
PS-99020-0087
SD-3069-GN***

This document was generated on 06/26/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[09-93-1500](#)