

D48 Euro Wall Mount 7-14 Watts Series

Features

- 230 VAC Input
- European Wall Plug In Style
- Rated for Continuous Duty
- Filtered
- Unregulated Outputs up to 12 Watts
- Safety Agency Approved/CE Compliant
- Impact Resistant Polycarbonate Enclosure
- Private Label Marking Available
- 1 Year Warranty
- Modified and Custom Designs Also Available
- Manufactured in China

Ault Model	Voltage DC	Minimum Current-Amps	Maximum Current-Amps	Maximum Watts
D48-051800-A000G	5	0	1.80	9.00
D48-061500-A000G	6	0	1.50	9.00
D48-071300-A000G	7	0	1.30	9.00
D48-081200-A000G	8	0	1.20	9.60
D48-091000-A000G	9	0	1.00	9.00
D48-100900-A000G	10	0	0.90	9.60
D48-120600-A000G	12	0	0.60	7.20
D48-120800-A000G	12	0	0.80	9.60
D48-121000-A000G	12	0	1.00	12.0
D48-140600-A000G	14	0	0.60	8.40
D48-150500-A000G	15	0	0.50	7.50
D48-151000-A000G	15	0	1.00	15.0
D48-180600-A000G	18	0	0.60	10.8
D48-200600-A000G	20	0	0.60	12.0
D48-220500-A000G	22	0	0.50	11.0
D48-240500-A000G	24	0	0.50	12.0
D48-240600-A000G	24	0	0.60	14.4

Input

- Voltage 230 VAC
- Line Frequency 50 Hz
- Connector Euro Wall Plug, No Ground

Electrical

- Topology DC Unregulated Power Supply
- Dielectric Withstand 3000 VAC primary-secondary
- Protection Current, Thermal or Energy Limiting
- EMI Complies with EMC Directives
- CE CE Compliant

Safety Approvals

EN60950

Environmental

- Operating Temperature 5° to 40° C with no derating
**This model only 0-50° C.
- Storage Temperature -30° to +85° C
- Relative Humidity 5% to 95% non-condensing
- Altitude 0-10,000 feet
- Cooling Convectional - non vented case

Mechanical

- Case Dimensions D48 - Euro Wall Plug
3.2 L x 2.2 W x 2.0 H (in)
81 L x 55 W x 48 H (mm)
- Case Material Black 94 V1 Polycarbonate
- Weight 18 ounces, 525 grams,
(excluding cord)
- Cord and Connector 6 ft., 2 Conductor, 22-24 AWG
Ault #3 Connector
Other Connectors Available

ONE YEAR WARRANTY

Ault Incorporated, 7105 Northland Terrace, Minneapolis, MN 55428

Contact Ault Inc. for all your custom design requirements. Phone: 763.592.1900 · Fax 763.592.1911

