


382A012-4/86-0 Product Details



382A012-4/86-0

Molded Parts

- Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Molded Part Type = Transition
- Family Name = 382A0
- Transition Type = Y
- 2 Branches/Legs
- General Purpose Application

TE Internal Number: 468963-000

Active

Documentation & Additional Information	
Product Drawings: - Transition, Y (PDF, English) Catalog Pages/Data Sheets: - None Available Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: - None Available	Additional Information: - Product Line Information Related Products: - Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - Molded Part Type = Transition - Family Name = 382A0 - Adhesive Description = High Performance Pre-Coat Adhesive - Size = 12 Mechanical Attachment: - Adhesive Pre-Coating = With Dimensions: 1st Branch/Leg Range (mm [in]) = 3.30 – 6.60 [0.130 – 0.260] 2nd Branch/Leg Range (mm [in]) = 3.30 – 6.60 [0.130 – 0.260] Body Features: - Transition Type = Y - Material = Polyolefin Flexible Modified Housing Features: - Material Systems Code = 10 - Max. Inside Diameter of Part (mm [in]) = 6.10 – 13.20 [0.240 – 0.520]	Configuration Features: - Number of Branches/Legs = 2 - Material Code = 4 Industry Standards: - Government/Industry Qualification = No - Approved Standards = DEF Std 59-97 Issue 3 Type DA, MIL-I-81765/2 Class II, UL224 E85831 - RoHS/ELV Compliance = RoHS compliant, ELV compliant - Lead Free Solder Processes = Not relevant for lead free process - RoHS/ELV Compliance History = Always was RoHS compliant Environmental: - Operating Temperature (°C) = -55 – +120 Operation/Application: - Application = General Purpose Purchasing Information: - Adhesive Code = 86 Other: - Brand = Raychem