





Heyco® CPV Solar Bulkhead Connectors

With Integral Sealing Ring for Creating a Liquid Tight Seal Through a Panel

| PART NO. | DESCRIPTION | PART DIMENSIONS | | | | | |
|----------|-------------|------------------------------------|-----------------------------------|------------------------------------|-----------------------------------|-----|------|
| | | A Max O.A. Length in. mm. | B Mounted Length in. mm. | C Wrenching Flats in. mm. | D Clearance Hole in. mm. | | |
| Black | | | | | | | |
| S6360 | CPV-P-BH | 2.08 | 52,8 | .147 | 37,3 | .98 | 24,9 |
| S6362 | CPV-N-BH | 1.44 | 36,5 | .83 | 21,0 | | |
| | | | | | | | |



- Bulkhead connectors mate with Heyco CPV Solar Connectors **creating a liquid tight seal through the panel**.
- Provided with an assembled metal locknut.
- Integral sealing ring ensures a superior seal at the mounting hole location, every time.
- Crimp to stranded wire 14 to 10 gauge for internal connections.
- 1/2" NPT thread for installation into 1/2" knock-out hole
- Polycarbonate construction for good chemical and impact resistance.
- Disconnection (PN S6390) and crimping tools (PN S6392 for 10 & 12 AWG wire) available. See page 6.
- RoHS and REACH compliant.
- UL recognized under File E344722.
- TUV certification No. R60033714.
- U.S. Patent No. 8398419B2.



| | |
|---------------------|---|
| Material | Polycarbonate |
| Certifications | UL Recognized under the Component Program of Underwriters' Laboratories File E344722. |
| Flammability Rating | VO |
| Temperature Rating | -40°F (-40°C) to 221°F (105°C) |
| IP Rating | IP 65 & IP 67 |

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Heyco:

S6360 S6362