


HBL1547-- Straight Blade Products, Elastogrip Series Conne Body



2-Pole 3Wire Grounding, 15A 125V, 150R, Yellow Elastomer, Dust Tight

Product Specifications

Product Type	
	Connectors
Body Style	Straight
Standard	NEMA
Amperage	15A
Voltage	125V
Poles and Wires	2 Pole, 3Wire Grounding
Hospital Grade ?	No
Plug/Connector Grade	Elastogrip
Enhancement	Dust Tight
Color	 Yellow
NEMA No.	5-15R
Cord Dia.	.300"-.655" (7.616.6)
Type	2 Pole, 3 Wire, Grounding
Rating	15A, 125V
Certification	UL Listed to UL498 File E1706, CSA Certified to C22.2 No. 42 File 280
IP Suitability	IP20
Housing Material	PVC-Yellow
Retainer Material	Polycarbonate-Clear
Cord Clamp Material	Nylon-Yellow
Contact Blades Material	.060" (1.5) Brass
Ground Contact Blade Material	.040" (1.0) Copper Alloy
Terminal Screw Material	#8-32 Brass, Multiple Drive
Ground Screw Material	#8-32 Brass, Multiple Drive (Green)
Contact Holder Material	Nylon-Natural
Power Contacts Material	.040" (1.0) Copper Alloy
Dielectric Voltage	Withstands 2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current factor of 75%..
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).
Terminal Accommodation	#14#10 AWG copper stranded or solid conductor only.
Product Identification	Ratings are a permanent part of the device.
Flammability	UL 94 HB or better.
Operating Temperatures	Maximum continuous 75°C, minimum 40°C (w/o impact).
M Drawings	Click here for MDrawing
Catalog Page	Click here for catalog page A26
Catalog Section	Click here for Section A
UPC Number	783585013039
Weight in LBs	0.200



NEMA Configuration