





REV.	DATE	ECR NO.	DESCRIPTION
NC	04/03/97	—	INITIAL RELEASE
A	05/01/04	—	UPDATE DRAWING FORMAT
B	10/27/08	—	ADD NOTES 1 AND 2



RECOMMENDED
CABLE STRIPPING DIM'S



STAMP "CONNEX"



NOTES:

1. CRIMP FERRULE HEX CRIMP SIZE .320" [8.13]
2. CRIMPED CONTACT PIN SQ. CRIMP .043" [1.09]
OR 12 INDENT CRIMP.

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
8						DRAWN	GRS	10/27/08							
7						CHECKED									
6						ISSUED				PART DESCRIPTION BNC CRIMP PLUG (RG6 PLENUM/BELDEN 1694A)					
5						SHEET	1 OF 1								
4	FERRULE	COPPER	NICKEL	1							PART NO. 112957				
3	CONTACT PIN	BRASS	GOLD	1											
2	INSULATOR	PTFE	NATURAL	1							DWG. NO.112957.DWG				
1	BODY	BRASS	NICKEL	1											
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE C:/112/112957.DWG					REV. B	SIZE A	SCALE NA		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112957](#)