




13			12		11		10		9		8		7		6		5		4		3		2		1									
PACKAGING SEE NOTE 4 SHT 1		4-6 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A				BULK		BULK								
		8-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS				TUBES		TUBES								
		DIM. M±0.25 MM				6.10 (.240)				6.10 (.240)				6.10 (.240)				6.10 (.240)				8.13 (.320)				8.13 (.320)								
		PLATING				150 TIN				15 GOLD				30 GOLD								15 GOLD				30 GOLD								
		DIM. H				2.54 (.100)				2.54 (.100)				2.54 (.100)				2.54 (.100)				4.57 (.180)				4.57 (.180)								
CKTS	DIM. A		DIM. B		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS								
	MM	IN	MM	IN																														
04	5.08	.200	2.54	.100	015-91-2040	015-91-6040	N/A	015-91-0040	015-91-6042	N/A	015-91-3040	015-91-6043	N/A	015-91-0048	015-91-5049	04	H	06	7.62	.300	5.08	.200	015-91-2060	015-91-6060	N/A	015-91-0060	015-91-6062	N/A	015-91-0068	015-91-5069	06			
08	10.16	.400	7.62	.300	015-91-2080	015-91-6080	015-91-3087	015-91-0080	015-91-6082	015-91-3086	015-91-3080	015-91-6083	015-91-3088	015-91-0088	015-91-5089	08		10	12.70	.500	10.16	.400	015-91-2100	015-91-6100	015-91-3107	015-91-0100	015-91-6102	015-91-3106	015-91-6103	015-91-3108	015-91-0108	015-91-5109	10	
12	15.24	.600	12.70	.500	015-91-2120	015-91-6120	015-91-3127	015-91-0120	015-91-6122	015-91-3126	015-91-3120	015-91-6123	015-91-3128	015-91-0128	015-91-5129	12		14	17.78	.700	15.24	.600	015-91-2140	015-91-6140	015-91-3147	015-91-0140	015-91-6142	015-91-3146	015-91-6143	015-91-3148	015-91-0148	015-91-5149	14	
16	20.32	.800	17.78	.700	015-91-2160	015-91-6160	015-91-3167	015-91-0160	015-91-6162	015-91-3166	015-91-3160	015-91-6163	015-91-3168	015-91-0168	015-91-5169	16		18	22.86	.900	20.32	.800	015-91-2180		015-91-3187	015-91-0180	015-91-3186	015-91-3180	015-91-3188	015-91-0188	015-91-5189	18		
20	25.40	1.000	22.86	.900	015-91-2200	015-91-6200	015-91-3207	015-91-0200	015-91-6202	015-91-3206	015-91-3200	015-91-6203	015-91-3208	015-91-0208	015-91-5209	20		22	27.94	1.100	25.40	1.000	015-91-2220		015-91-3227	015-91-0220	015-91-3226	015-91-3220	015-91-3228	015-91-0228	015-91-5229	22		
24	30.48	1.200	27.94	1.100	015-91-2240		015-91-3247	015-91-0240		015-91-3246	015-91-3240		015-91-3248	015-91-0248	015-91-5249	24		26	33.02	1.300	30.48	1.200	015-91-2260	015-91-6260	015-91-3267	015-91-0260	015-91-6262	015-91-3266	015-91-3260	015-91-3268	015-91-0268	015-91-5269	26	
28	35.56	1.400	33.02	1.300	015-91-2280		015-91-3287	015-91-0280		015-91-3286	015-91-3280		015-91-3288	015-91-0288	015-91-5289	28		30	38.10	1.500	35.56	1.400	015-91-2300		015-91-3307	015-91-0300	015-91-3306	015-91-3300	015-91-3308	015-91-0308	015-91-5309	30		
32	40.64	1.600	38.10	1.500	015-91-2320		015-91-3327	015-91-0320		015-91-3326	015-91-3320		015-91-3328	015-91-0328	015-91-5329	32		34	43.18	1.700	40.64	1.600	015-91-2340		015-91-3347	015-91-0340	015-91-3346	015-91-3340	015-91-3348	015-91-0348	015-91-5349	34		
36	45.72	1.800	43.18	1.700	015-91-2360		015-91-3367	015-91-0360		015-91-3366	015-91-3360		015-91-3368	015-91-0368	015-91-5369	36		38	48.26	1.900	45.72	1.800	015-91-2380		015-91-3387	015-91-0380	015-91-3386	015-91-3380	015-91-3388	015-91-0388	015-91-5389	38		
40	50.80	2.000	48.26	1.900	015-91-2400	015-91-6400	015-91-3407	015-91-0400	015-91-6402	015-91-3406	015-91-3400	015-91-6403	015-91-3408	015-91-0408	015-91-5409	40		42	53.34	2.100	50.80	2.000	015-91-2420		015-91-3427	015-91-0420	015-91-3426	015-91-3420	015-91-3428	015-91-0428	015-91-5429	42		
44	55.88	2.200	53.34	2.100	015-91-2440		015-91-3447	015-91-0440		015-91-3446	015-91-3440		015-91-3448	015-91-0448	015-91-5449	44		46	58.42	2.300	55.88	2.200	015-91-2460		015-91-3467	015-91-0460	015-91-3466	015-91-3460	015-91-3468	015-91-0468	015-91-5469	46		
48	60.96	2.400	58.42	2.300	015-91-2480		015-91-3487	015-91-0480		015-91-3486	015-91-3480		015-91-3488	015-91-0488	015-91-5489	48		50	63.50	2.500	60.96	2.400	015-91-2500	015-91-6500	015-91-3507	015-91-0500	015-91-6502	015-91-3506	015-91-3500	015-91-6503	015-91-3508	015-91-0508	015-91-5509	50
52	66.04	2.600	63.50	2.500	015-91-2520		015-91-3527	015-91-0520		015-91-3526	015-91-3520		015-91-3528	015-91-0528	015-91-5529	52		54	68.58	2.700	66.04	2.600	015-91-2540		015-91-3547	015-91-0540	015-91-3546	015-91-3540	015-91-3548	015-91-0548	015-91-5549	54		
56	71.12	2.800	68.58	2.700	015-91-2560		015-91-3567	015-91-0560		015-91-3566	015-91-3560		015-91-3568	015-91-0568	015-91-5569	56		58	73.66	2.900	71.12	2.800	015-91-2580		015-91-3587	015-91-0580	015-91-3586	015-91-3580	015-91-3588	015-91-0588	015-91-5589	58		
60	76.20	3.000	73.66	2.900	015-91-2600		015-91-3607	015-91-0600		015-91-3606	015-91-3600		015-91-3608	015-91-0608	015-91-5609	60		62	78.74	3.100	76.20	3.000	015-91-2620		015-91-3627	015-91-0620	015-91-3626	015-91-3620	015-91-3628	015-91-0628	015-91-5629	62		
64	81.28	3.200	78.74	3.100	015-91-2640		015-91-3647	015-91-0640		015-91-3646	015-91-3640		015-91-3648	015-91-0648	015-91-5649	64		66	83.82	3.300	81.28	3.200	015-91-2660		015-91-3667	015-91-0660	015-91-3666	015-91-3660	015-91-3668	015-91-0668	015-91-5669	66		
68	86.36	3.400	83.82	3.300	015-91-2680		015-91-3687	015-91-0680		015-91-3686	015-91-3680		015-91-3688	015-91-0688	015-91-5689	68		70	88.90	3.500	86.36	3.400	015-91-2700		015-91-3707	015-91-0700	015-91-3706	015-91-3700	015-91-3708	015-91-0708	015-91-5709	70		
72	91.44	3.600	88.90	3.500	015-91-2720		015-91-3727	015-91-0720		015-91-3726	015-91-3720		015-91-3728	015-91-0728	015-91-5729	72		74	93.98	3.700	91.44	3.600	015-91-2740		015-91-3747	015-91-0740	015-91-3746	015-91-3740	015-91-3748	015-91-0748	015-91-5749	74		
76	96.52	3.800	93.98	3.700	015-91-2760		015-91-3767	015-91-0760		015-91-3766	015-91-3760		015-91-3768	015-91-0768	015-91-5769	76		78	99.06	3.900	96.52	3.800	015-91-2780		015-91-3787	015-91-0780	015-91-3786	015-91-3780	015-91-3788	015-91-0788	015-91-5789	78		
80	101.60	4.000	99.06	3.900	015-91-2800		015-91-3807	015-91-0800		015-91-3806	015-91-3800		015-91-3808	015-91-0808	015-91-5809	80		82	104.14	4.100	101.60	4.000	71308-0082		71308-0482	71308-0182	71308-0582	71308-0282	71308-0682	71308-1182	71308-1282	82		
84	106.68	4.200	104.14	4.100	71308-0084		71308-0484	71308-0184		71308-0584	71308-0284		71308-0684	71308-1184	71308-1284	84		86	109.22	4.300	106.68	4.200	71308-0086		71308-0486	71308-0186	71308-0586	71308-0286	71308-0686	71308-1186	71308-1286	86		
88	111.76	4.400	109.22	4.300	71308-0088		71308-0488	71308-0188		71308-0588	71308-0288		71308-0688	71308-1188	71308-1288	88	90	114.30	4.500	111.76	4.400	71308-0090		71308-0490	71308-0190	71308-0590	71308-0290	71308-0690	71308-1190	71308-1290	90			
92	116.84	4.600	114.30	4.500	71308-0092		71308-0492	71308-0192		71308-0592	71308-0292		71308-0692	71308-1192	71308-1292	92	94	119.38	4.700	116.84	4.600	71308-0094		71308-0494	71308-0194	71308-0594	71308-0294	71308-0694	71308-1194	71308-1294	94			
96	121.92	4.800	119.38	4.700	71308-0096		71308-0496	71308-0196		71308-0596	71308-0296		71308-0696	71308-1196	71308-1296	96	98	124.46	4.900	121.92	4.800	71308-0098		71308-0498	71308-0198	71308-0598	71308-0298	71308-0698	71308-1198	71308-1298	98			
100	127.00	5.000	124.46	4.900	71308-0101		71308-0500	71308-0200		71308-0600	71308-0300		71308-0700		71308-1300	100																		

13		12		11				10		9		8		7		6		5		4		3		2		1	
J		IN TAPE AND REEL WITH SHALLOW POCKET TAPE												BULK / IN TUBES										J			
		PACKAGING SEE NOTE 4. SHT 1		4-8 CKT		TAPE-N-REEL W/ VAC CAPS		TAPE-N-REEL W/ VAC CAPS										BULK		BULK							
				10-100 CKT		TAPE-N-REEL W/ VAC CAPS		TAPE-N-REEL W/ VAC CAPS										TUBES		TUBES							
		DIM. M±0.25 MM				6.10 (.240)		6.10 (.240)										8.13 (.320)		13.59 (.535)							
		PLATING				30 GOLD		15 GOLD										150 TIN		150 TIN							
		DIM. H				2.54 (.100)		2.54 (.100)										4.57 (.180)		4.57 (.180)							
I		CKTS	DIM. A		DIM. B		EDP NUMBER	EDP NUMBER					EDP NUMBER	EDP NUMBER	CKTS												
			MM	IN	MM	IN																					
		04	5.08	.200	2.54	.100									04												
		06	7.62	.300	5.08	.200		015-91-6068							06												
		08	10.16	.400	7.62	.300		015-91-6088							08												
		10	12.70	.500	10.16	.400		015-91-6108					713088010	71308-8210	10												
		12	15.24	.600	12.70	.500									12												
H		14	17.78	.700	15.24	.600	015-91-6148								14												
		16	20.32	.800	17.78	.700							713088016		16												
		18	22.86	.900	20.32	.800									18												
		20	25.40	1.000	22.86	.900									20												
		22	27.94	1.100	25.40	1.000									22												
		24	30.48	1.200	27.94	1.100									24												
		26	33.02	1.300	30.48	1.200									26												
G		28	35.56	1.400	33.02	1.300									28												
		30	38.10	1.500	35.56	1.400									30												
		32	40.64	1.600	38.10	1.500									32												
		34	43.18	1.700	40.64	1.600									34												
		36	45.72	1.800	43.18	1.700									36												
		38	48.26	1.900	45.72	1.800									38												
		40	50.80	2.000	48.26	1.900									40												
F		42	53.34	2.100	50.80	2.000									42												
		44	55.88	2.200	53.34	2.100									44												
		46	58.42	2.300	55.88	2.200									46												
		48	60.96	2.400	58.42	2.300									48												
		50	63.50	2.500	60.96	2.400									50												
		52	66.04	2.600	63.50	2.500									52												
		54	68.58	2.700	66.04	2.600									54												
E		56	71.12	2.800	68.58	2.700									56												
		58	73.66	2.900	71.12	2.800									58												
		60	76.20	3.000	73.66	2.900									60												
		62	78.74	3.100	76.20	3.000									62												
		64	81.28	3.200	78.74	3.100									64												
D		66	83.82	3.300	81.28	3.200									66												
		68	86.36	3.400	83.82	3.300									68												
		70	88.90	3.500	86.36	3.400									70												
		72	91.44	3.600	88.90	3.500									72												
		74	93.98	3.700	91.44	3.600									74												
		76	96.52	3.800	93.98	3.700									76												
C		78	99.06	3.900	96.52	3.800									78												
		80	101.60	4.000	99.06	3.900									80												
		82	104.14	4.100	101.60	4.000									82												
		84	106.68	4.200	104.14	4.100									84												
		86	109.22	4.300	106.68	4.200									86												
		88	111.76	4.400	109.22	4.300									88												
B		90	114.30	4.500	111.76	4.400									90												
		92	116.84	4.600	114.30	4.500									92												
		94	119.38	4.700	116.84	4.600									94												
		96	121.92	4.800	119.38	4.700									96												
		98	124.46	4.900	121.92	4.800									98												
		100	127.00	5.000	124.46	4.900									100												
A		NO PEG VERSION										SALES ASSY INSULATOR DUAL ROW SMT W/BREAK-OFF .025SQ PIN GULLWING .100										A					
		(ALSO SEE SHEET 2)										molex															
		SEE SHEET 1 EC NO: UCP2015-0081 DRAWN BY: CHKDANGUYEN CHKD:ANGUYEN APPR:FSMITH K7										QUALITY SYMBOLS ▽=0 ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ±.005 3 PLACES ±.010 2 PLACES ±.015 1 PLACE ±.020 0 PLACE ±.030		DIMENSION STYLE MM/IN DRAWN BY: KMS CHECKED BY: KMS APPROVED BY: KMS		SCALE INCH TITLE SALES ASSY INSULATOR DUAL ROW SMT W/BREAK-OFF .025SQ PIN GULLWING .100		DESIGN UNITS INCH THIRD ANGLE PROJECTION		DOCUMENT NO. SD-71308-001		SHEET NO. 3 OF 6			
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																									

13		12		11		10		9		8		7		6		5		4		3		2		1																	
J	PACKAGING SEE NOTE 4 SHT 1						4-8 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		BULK		BULK																				
							10-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TUBES		TUBES																
							DIM. M±0.25 MM						6.10 (.240)						6.10 (.240)						6.10 (.240)						8.13 (.320)		8.13 (.320)		8.13 (.320)						
							PLATING						150 TIN						15 GOLD						30 GOLD						150 TIN		15 GOLD		30 GOLD						
							DIM. H						2.54 (.100)						2.54 (.100)						2.54 (.100)						4.57 (.180)		4.57 (.180)		4.57 (.180)						
I	CKTS	DIM. A		DIM. B		DIM. C		EDP		EDP		EDP		EDP		EDP		EDP		EDP		EDP		EDP		CKTS															
		MM	IN	MM	IN	MM	IN	NUMBER	NUMBER	NUMBER	NUMBER	NUMBER	NUMBER	NUMBER	NUMBER	NUMBER	NUMBER	NUMBER	NUMBER	NUMBER	NUMBER	NUMBER	NUMBER																		
H	04	5.08	.200	2.54	.100	----	----	015-91-1041	015-91-6044	015-91-1042	015-91-6045	015-91-1043	015-91-6046	015-91-1044	015-91-0047	015-91-1040								04																	
	06	7.62	.300	5.08	.200	2.54	.100	015-91-1061	015-91-6064	015-91-1062	015-91-6065	015-91-1063	015-91-6066	015-91-1064	015-91-0067	015-91-1060								06																	
	08	10.16	.400	7.62	.300	5.08	.200	015-91-1081	015-91-6084	015-91-1082	015-91-6085	015-91-1083	015-91-6086	015-91-1084	015-91-0087	015-91-1080								08																	
	10	12.70	.500	10.16	.400	7.62	.300	015-91-1101	015-91-6104	015-91-1102	015-91-6105	015-91-1103	015-91-6106	015-91-1104	015-91-0107	015-91-1100								10																	
	12	15.24	.600	12.70	.500	10.16	.400	015-91-1121		015-91-1122		015-91-1123		015-91-1124	015-91-0127	015-91-1120								12																	
	14	17.78	.700	15.24	.600	12.70	.500	015-91-1141	015-91-6144	015-91-1142	015-91-6145	015-91-1143	015-91-6146	015-91-1144	015-91-0147	015-91-1140								14																	
	16	20.32	.800	17.78	.700	15.24	.600	015-91-1161	015-91-6164	015-91-1162	015-91-6165	015-91-1163	015-91-6166	015-91-1164	015-91-0167	015-91-1160								16																	
	18	22.86	.900	20.32	.800	17.78	.700	015-91-1181		015-91-1182		015-91-1183		015-91-1184	015-91-0187	015-91-1180								18																	
	20	25.40	1.000	22.86	.900	20.32	.800	015-91-1201		015-91-1202		015-91-1203		015-91-1204	015-91-0207	015-91-1200								20																	
	22	27.94	1.100	25.40	1.000	22.86	.900	015-91-1221		015-91-1222		015-91-1223		015-91-1224	015-91-0227	015-91-1220								22																	
G	24	30.48	1.200	27.94	1.100	25.40	1.000	015-91-1241	71308-6901	015-91-1242		015-91-1243		015-91-1244	015-91-0247	015-91-1240								24																	
	26	33.02	1.300	30.48	1.200	27.94	1.100	015-91-1261		015-91-1262		015-91-1263		015-91-1264	015-91-0267	015-91-1260								26																	
	28	35.56	1.400	33.02	1.300	30.48	1.200	015-91-1281		015-91-1282		015-91-1283		015-91-1284	015-91-0287	015-91-1280								28																	
	30	38.10	1.500	35.56	1.400	33.02	1.300	015-91-1301		015-91-1302		015-91-1303		015-91-1304	015-91-0307	015-91-1300								30																	
	32	40.64	1.600	38.10	1.500	35.56	1.400	015-91-1321		015-91-1322		015-91-1323		015-91-1324	015-91-0327	015-91-1320								32																	
	34	43.18	1.700	40.64	1.600	38.10	1.500	015-91-1341		015-91-1342		015-91-1343		015-91-1344	015-91-0347	015-91-1340								34																	
	36	45.72	1.800	43.18	1.700	40.64	1.600	015-91-1361		015-91-1362		015-91-1363		015-91-1364	015-91-0367	015-91-1360								36																	
	38	48.26	1.900	45.72	1.800	43.18	1.700	015-91-1381		015-91-1382		015-91-1383		015-91-1384	015-91-0387	015-91-1380								38																	
	40	50.80	2.000	48.26	1.900	45.72	1.800	015-91-1401		015-91-1402		015-91-1403		015-91-1404	015-91-0407	015-91-1400								40																	
	42	53.34	2.100	50.80	2.000	48.26	1.900	015-91-1421		015-91-1422		015-91-1423		015-91-1424	015-91-0427	015-91-1420								42																	
F	44	55.88	2.200	53.34	2.100	50.80	2.000	015-91-1441		015-91-1442		015-91-1443		015-91-1444	015-91-0447	015-91-1440								44																	
	46	58.42	2.300	55.88	2.200	53.34	2.100	015-91-1461		015-91-1462		015-91-1463		015-91-1464	015-91-0467	015-91-1460								46																	
	48	60.96	2.400	58.42	2.300	55.88	2.200	015-91-1481		015-91-1482		015-91-1483		015-91-1484	015-91-0487	015-91-1480								48																	
	50	63.50	2.500	60.96	2.400	58.42	2.300	015-91-1501	015-91-6504	015-91-1502	015-91-6505	015-91-1503	015-91-6506	015-91-1504	015-91-0507	015-91-1500								50																	
	52	66.04	2.600	63.50	2.500	60.96	2.400	015-91-1521		015-91-1522		015-91-1523	71308-5203	015-91-1524	015-91-0527	015-91-1520								52																	
	54	68.58	2.700	66.04	2.600	63.50	2.500	015-91-1541		015-91-1542		015-91-1543		015-91-1544	015-91-0547	015-91-1540								54																	
	56	71.12	2.800	68.58	2.700	66.04	2.600	015-91-1561		015-91-1562		015-91-1563		015-91-1564	015-91-0567	015-91-1560								56																	
	58	73.66	2.900	71.12	2.800	68.58	2.700	015-91-1581		015-91-1582		015-91-1583		015-91-1584	015-91-0587	015-91-1580								58																	
	60	76.20	3.000	73.66	2.900	71.12	2.800	015-91-1601		015-91-1602		015-91-1603		015-91-1604	015-91-0607	015-91-1600								60																	
	62	78.74	3.100	76.20	3.000	73.66	2.900	015-91-1621		015-91-1622		015-91-1623		015-91-1624	015-91-0627	015-91-1620								62																	
E	64	81.28	3.200	78.74	3.100	76.20	3.000	015-91-1641		015-91-1642		015-91-1643		015-91-1644	015-91-0647	015-91-1640								64																	
	66	83.82	3.300	81.28	3.200	78.74	3.100	015-91-1661		015-91-1662		015-91-1663		015-91-1664	015-91-0667	015-91-1660								66																	
	68	86.36	3.400	83.82	3.300	81.28	3.200	015-91-1681		015-91-1682		015-91-1683		015-91-1684	015-91-0687	015-91-1680								68																	
	70	88.90	3.500	86.36	3.400	83.82	3.300	015-91-1701		015-91-1702		015-91-1703		015-91-1704	015-91-0707	015-91-1700								70																	
	72	91.44	3.600	88.90	3.500	86.36	3.400	015-91-1721		015-91-1722		015-91-1723		015-91-1724	015-91-0727	015-91-1720								72																	
	74	93.98	3.700	91.44	3.600	88.90	3.500	015-91-1741		015-91-1742		015-91-1743		015-91-1744	015-91-0747	015-91-1740								74																	
	76	96.52	3.800	93.98	3.700	91.44	3.600	015-91-1761		015-91-1762		015-91-1763		015-91-1764	015-91-0767	015-91-1760								76																	
	78	99.06	3.900	96.52	3.800	93.98	3.700	015-91-1781		015-91-1782		015-91-1783		015-91-1784	015-91-0787	015-91-1780								78																	
	80	101.60	4.000	99.06	3.900	96.52	3.800	015-91-1801		015-91-1802		015-91-1803		015-91-1804	015-91-0807	015-91-1800								80																	
	82	104.14	4.100	101.60	4.000	99.06	3.900	71308-4082		71308-4182		71308-4282		71308-5082	71308-5182	71308-5282								82																	
C	84	106.68	4.200	104.14	4.100	101.60	4.000	71308-4084		71308-4184		71308-4284		71308-5084	71308-5184	71308-5284								84																	
	86	109.22	4.300	106.68	4.200	104.14	4.100	71308-4086		71308-4186		71308-4286		71308-5086	71308-5186	71308-5286								86																	
	88	111.76	4.400	109.22	4.300	106.68	4.200	71308-4088		71308-4188		71308-4288		71308-5088	71308-5188	71308-5288								88																	
	90	114.30	4.500	111.76	4.400	109.22	4.300	71308-4090		71308-4190		71308-4290		71308-5090	71308-5190	71308-5290								90																	
	92	116.84	4.600	114.30	4.500	111.76	4.400	71308-4092		71308-4192		71308-4292		71308-5092	71308-5192	71308-5292								92																	
	94	119.38	4.700	116.84	4.600	114.30	4.500	71308-4094		71308-4194		71308-4294		71308-5094	71308-5194	71308-5294								94																	
	96	121.92	4.800	119.38	4.700	116.84	4.600	71308-4096		71308-4196		71308-4296		71308-5096	71308-5196	71308-5296								96																	
	98	124.46	4.900	121.92	4.800	119.38	4.700	71308-4098		71308-4198		71308-4298		71308-5098	71308-5198	71308-5298								98																	
	100	127.00	5.000	124.46	4.900	121.92	4.800	71308-4100		71308-4200		71308-4300		71308-5100	71308-5200	71308-5300								100																	
	B	LONG PEG VERSION (.130")																								SEE SHEET 1 EC NO: UCP2015-0081 DRAWN:MK/PPER 2014/05/22 CHKD:NGUYEN 2014/11/26 APPR:FSM/TH 2015/01/08	REV K7	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		B			
A																									K7	REV	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE		DESIGN UNITS INCH		THIRD ANGLE PROJECTION		A		
																								K7		REV		DESCRIPTION		QUALITY SYMBOLS ▽=0 ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE		DESIGN UNITS INCH		THIRD ANGLE PRO	

	13	12	11	10	9	8	7	6	5	4	3	2	1				
J			PACKAGING SEE NOTE 4 SHT 1	4-8 CKT	BULK	TAPE-N-REEL W/ VAC CAPS	BULK	TAPE-N-REEL W/ VAC CAPS	TAPE-N-REEL W/ VAC CAPS					J			
10-100 CKT				TUBES	TAPE-N-REEL W/ VAC CAPS	TUBES	TAPE-N-REEL W/ VAC CAPS	TAPE-N-REEL W/ VAC CAPS									
DIM. M±0.25 MM			6.10 (.240)		6.10 (.240)		8.13 (.320)										
PLATING			30 GOLD		150 TIN		150 TIN										
DIM. H			2.54 (.100)		2.54 (.100)		4.57 (.180)										
I	CKTS	DIM. A		DIM. B		DIM. C		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS		
		MM	IN	MM	IN	MM	IN										
	04	5.08	.200	2.54	.100	----	----	015-91-1048	015-91-6047						04		
	06	7.62	.300	5.08	.200	2.54	.100	015-91-1068	015-91-6067	71308-6106	71308-6206				06		
	08	10.16	.400	7.62	.300	5.08	.200	015-91-1088	015-91-6087	71308-6108	71308-6208				08		
	10	12.70	.500	10.16	.400	7.62	.300	015-91-1108	015-91-6107	71308-6110	71308-6210				10		
	12	15.24	.600	12.70	.500	10.16	.400	015-91-1128							12		
	14	17.78	.700	15.24	.600	12.70	.500	015-91-1148	015-91-6147						14		
	16	20.32	.800	17.78	.700	15.24	.600	015-91-1168	015-91-6167						16		
	18	22.86	.900	20.32	.800	17.78	.700	015-91-1188							18		
	20	25.40	1.000	22.86	.900	20.32	.800	015-91-1208	015-91-6207						20		
	22	27.94	1.100	25.40	1.000	22.86	.900	015-91-1228							22		
	24	30.48	1.200	27.94	1.100	25.40	1.000	015-91-1248							24		
	26	33.02	1.300	30.48	1.200	27.94	1.100	015-91-1268		71308-6126		71308-8426			26		
	28	35.56	1.400	33.02	1.300	30.48	1.200	015-91-1288							28		
	30	38.10	1.500	35.56	1.400	33.02	1.300	015-91-1308							30		
	32	40.64	1.600	38.10	1.500	35.56	1.400	015-91-1328							32		
	34	43.18	1.700	40.64	1.600	38.10	1.500	015-91-1348							34		
	36	45.72	1.800	43.18	1.700	40.64	1.600	015-91-1368							36		
	38	48.26	1.900	45.72	1.800	43.18	1.700	015-91-1388							38		
	40	50.80	2.000	48.26	1.900	45.72	1.800	015-91-1408							40		
	42	53.34	2.100	50.80	2.000	48.26	1.900	015-91-1428							42		
	44	55.88	2.200	53.34	2.100	50.80	2.000	015-91-1448							44		
	46	58.42	2.300	55.88	2.200	53.34	2.100	015-91-1468							46		
	48	60.96	2.400	58.42	2.300	55.88	2.200	015-91-1488							48		
	50	63.50	2.500	60.96	2.400	58.42	2.300	015-91-1508	015-91-6507						50		
	52	66.04	2.600	63.50	2.500	60.96	2.400	015-91-1528							52		
	54	68.58	2.700	66.04	2.600	63.50	2.500	015-91-1548							54		
	56	71.12	2.800	68.58	2.700	66.04	2.600	015-91-1568							56		
	58	73.66	2.900	71.12	2.800	68.58	2.700	015-91-1588							58		
	60	76.20	3.000	73.66	2.900	71.12	2.800	015-91-1608							60		
	62	78.74	3.100	76.20	3.000	73.66	2.900	015-91-1628							62		
	64	81.28	3.200	78.74	3.100	76.20	3.000	015-91-1648							64		
	66	83.82	3.300	81.28	3.200	78.74	3.100	015-91-1668							66		
	68	86.36	3.400	83.82	3.300	81.28	3.200	015-91-1688							68		
	70	88.90	3.500	86.36	3.400	83.82	3.300	015-91-1708							70		
	72	91.44	3.600	88.90	3.500	86.36	3.400	015-91-1728							72		
	74	93.98	3.700	91.44	3.600	88.90	3.500	015-91-1748							74		
	76	96.52	3.800	93.98	3.700	91.44	3.600	015-91-1768							76		
	78	99.06	3.900	96.52	3.800	93.98	3.700	015-91-1788							78		
	80	101.60	4.000	99.06	3.900	96.52	3.800	015-91-1808							80		
	82	104.14	4.100	101.60	4.000	99.06	3.900	71308-6082							82		
	84	106.68	4.200	104.14	4.100	101.60	4.000	71308-6084							84		
	86	109.22	4.300	106.68	4.200	104.14	4.100	71308-6086							86		
	88	111.76	4.400	109.22	4.300	106.68	4.200	71308-6088							88		
	90	114.30	4.500	111.76	4.400	109.22	4.300	71308-6090							90		
	92	116.84	4.600	114.30	4.500	111.76	4.400	71308-6092							92		
	94	119.38	4.700	116.84	4.600	114.30	4.500	71308-6094							94		
	96	121.92	4.800	119.38	4.700	116.84	4.600	71308-6096							96		
	98	124.46	4.900	121.92	4.800	119.38	4.700	71308-6098							98		
	100	127.00	5.000	124.46	4.900	121.92	4.800	71308-6100							100		
B	SHORT PEG VERSION (.055")														B		
A															A		
REMOVE 15-91-6407 EC NO: UCP2015-0081 DRAWN/KIPPER 2014/05/22 CHKD/NGUYEN 2014/11/26 APPR/FSMITH 2015/01/08		REV		DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
K7						▽=0		mm INCH		DRAWN BY DATE		TITLE					
						▽=0		4 PLACES ± --- ± ---		KMS 1999/10/15		SALES ASSY INSULATOR DUAL ROW SMT W/BREAK-OFF .025SQ PIN GULLWING .100					
						▽=0		3 PLACES ± --- ±.005		CHECKED BY DATE							
								2 PLACES ± 0.13 ±.010		KMS 1999/10/15		molex					
								1 PLACE ± 0.25 ± ---		APPROVED BY DATE							
								0 PLACE ± --- ± ---		KMS 1999/10/15							
								ANGULAR ±1/2°		MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
								DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-71308-001		5 OF 6			
								SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
lb_frame_C_P_AM.T Rev. G 2012/01/11		12	11	10	9	8	7	6	5	4	3	2	1				

		13		12		11		10		9		8		7		6		5		4		3		2		1											
J		PACKAGING SEE NOTE 4, SHT 1		4-6 CKT		BULK		TAPE-N-REEL W/VAC CAPS		N/A		4-8 CKT		TAPE-N-REEL W/VAC CAPS		BULK		BULK		LONG PEG VERSION (.130")		SHORT PEG VERSION (.055")															
						TUBES		TAPE-N-REEL W/VAC CAPS		TUBES W/ VAC CAPS				10-100 CKT		TAPE-N-REEL W/VAC CAPS		TUBES		TUBES		TUBES								BULK		TAPE-N-REEL W/ VAC CAPS					
				8-100 CKT																																	