

Direct Links

Cross Reference

RoHS/LF P/N search

Document & Drawing search

Application tooling

Services

Contact us

Distributor list

Pricing request

Order samples

Literature

Brochures & catalogs

Product documentation

Technical library

Start > Search=bibs-350-5* > BIBS-350-5

BIBS-350-5



BIBS-350-5

350-10, 1-SIDE,UNITAP

ACTIVE

Customer Drawing

RoHS compatible

Electrical division

Email Datasheet Print Datasheet

FCI Brings You More

- Contact our sales/technical support
- Sample request
- Price request

Download document

Literature

- > Oxide Inhibitor Unitap Material Safety Data Sheet
- > Power solutions Product Focus
- > Insulated Multiple Connectors Brochures
- > Aluminum Products Brochure
- > UNITAP Insulated Multiple Tap Connectors Brochure
- > Renewable Energy Products Brochure
- > EC&M Catalog
- > Connector Theory and Application Brochure

Application Tooling

- > Electrical Tooling

Specifications

General	Dimensional	Physical	Approvals / Certifications	Other Features
<u>General</u>				
Number of Ports			5	
<u>Dimensional</u>				
Height (in)			2.5 in.	
Length (in)			4.95 in.	
Width (in)			2.32 in.	
Wire Entry			Single	
Hex Size (Key)			5/16 in.	
<u>Physical</u>				
Conductor Size			250 kcmil	
			4/0 AWG	
			2/0 AWG	
			3/0 AWG	
			2 AWG	
			1 AWG	
			4 AWG	
			1/0 AWG	
			350 kcmil	
			8 AWG	
Conductor Size (Range)			10 AWG to 350 kcmi	
<u>Approvals / Certifications</u>				
UL Listed			Yes	
CSA Certified			No	
<u>Other Features</u>				
UPC			78181013350	
Keyword			unitap	