


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.*	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS- SECTION	WEIGHT lbs./100pcs (g)
	MIN. in (mm)	MAX. in (mm)									
SST1M	.06 (1.5)	.78 (20)	.035 (.9)	.095 (2.4)	.150 (3.8)	.125 (3.2)	.175 (4.5)	4.0 (102)	18 (80)	MINIATURE	.06 (25)
SST1.5M	.06 (1.5)	1.25 (32)	.037 (.9)	.095 (2.4)	.150 (3.8)	.125 (3.2)	.175 (4.5)	5.5 (140)	18 (80)	MINIATURE	.07 (32)
SST1.5I	.06 (1.5)	1.25 (32)	.037 (.9)	.135 (3.4)	.210 (5.3)	.147 (3.7)	.240 (6.1)	5.3 (137)	40 (178)	INTERMEDIATE	.12 (55)
SST2I	.06 (1.5)	2.00 (51)	.040 (1.0)	.135 (3.4)	.210 (5.3)	.147 (3.7)	.240 (6.1)	8.1 (206)	40 (178)	INTERMEDIATE	.17 (77)
SST3I	.06 (1.5)	3.00 (76)	.040 (1.0)	.135 (3.4)	.210 (5.3)	.147 (3.7)	.240 (6.1)	11.0 (279)	40 (178)	INTERMEDIATE	.24 (110)
SST4I	.06 (1.5)	4.00 (102)	.040 (1.0)	.135 (3.4)	.210 (5.3)	.147 (3.7)	.240 (6.1)	14.7 (375)	40 (178)	INTERMEDIATE	.31 (142)

NOTES:

- *1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
2) RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.

PANDUIT CORP. TINLEY PARK, ILLINOIS

STA-STRAP CABLE TIES SS SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± ---- (.XXX) ± .020(.51)
(.XX) ± .02(.5) ANGLES ± ----

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
JABO

MAT'L;

SCALE	NONE
-------	------

DATE	11-27-01
------	----------

NYLON 6.6

DRAWING NO.
SS - 5550
SHEET 1 OF 3

DWG
A
SIZE

5	4-19-05	ERW		METRIC CONVERSION CORRECTIONS	5550	5			
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		