









NOTE:
MATERIAL:
HOUSING: PBT+30%GF (UL 94V-0)
INSULATOR Color: Black
SHELL:BRASS C2680-H T=0.3mm
TERMINAL:PHOSPHOR BRONZE C5191-H T=0.20mm
SPECIFICATION:
VOLTAGE CURRENT RATING:1AMP 30V DC
INSULATION RESISTANCE:1000MΩ MIN
CONTACT RESISTANCE TERMINAL:30mΩ MAX
WITHSTANDING VOLTAGE:500V AC
MATING FORCE:30N MAX
UNMATING FORCE:10N MIN

RECOMMEND PCB LAYOUT



Pin Number	Signal Name
1	VBUS
2	D -
3	D +
4	GND
Shield	Shield

11/12/17	XIE	EG-N1112018	(新開模將原來四彈片加寬，增加插拔耐久力)		A1
11/08/05	XIE		NEW DWG		A0
DATE	DR.BY	ECN.NO.	DESCRIPTION	MARK	VER.

-TOLERANCES-

CnC Tech,LLC



TITLE: USB 4P A/F DIP 90度側插式
三只腳成品

X.X	±0.30	X.X°	±3.00°	APPD:	PRODUCT NO: 1001-008-01001
X.XX	±0.25	X.XX°	±2.00°	CHECK:	DATE SCALE UNIT TYPE PAGE
X.XXX ±0.15	X.XXX° ±1.00°	DRAW:	2011.08.05	1:1 mm Z	1 / 1