

MP-381191-5-8A Product Details



MP-381191-5-8A

TE Internal Number: F27596-000



Label ID Products

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Labels
- Region = Not Specified
- Printer Type = Thermal Transfer
- Label Height = 19.10 mm
- Label Width = 38.10 mm

Documentation & Additional Information	
Product Drawings: • None Available Catalog Pages/Data Sheets: • Label ID Products (PDF, English) Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: • None Available	Additional Information: • Product Line Information Related Products: • Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: • Product Type = Labels • Series = MP • Color = Silver Electrical Characteristics: • Printer Type = Thermal Transfer • Web Width (mm [in]) = 87.60 [3.450] Body Features: • Material = Metalized Polyester • Horizontal Repeat (mm [in]) = 43.2 [1.7] • Recommended Printer = T308S • Recommended Ribbon = 1330-0607-10 Configuration Features: • Number of Labels Across = 2 Industry Standards: • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant Printer/Label Features: • Label Height (mm [in]) = 19.10 [0.750] • Label Width (mm [in]) = 38.10 [1.500] • Tamper Evident = No • Label Type = Die-Cut • Adhesive Type = Permanent Acrylic • Vertical Repeat (mm [in]) = 22.20 [0.875]	Identification Marking: • Energy Label Type = Pressure Sensitive Environmental: • Operating Temperature (°C [°F]) = -40 - +150 [-40 - +302] Conditions for Usage: • Energy Product = Yes Packaging Features: • Packaging Quantity = 5,000 Product Availability: • Region = Not Specified Other: • Brand = TE Connectivity