

Model EGAXT3 Accelerometer

Miniature Triaxial Design
DC Response
10,000 g Overrange Stops
Broad Temperature Range


The Model EGAXT3 miniature triaxial accelerometer combines a damping ratio of 0.7 (Nominal) with built-in overrange stops that are set to protect the unit against 10,000g shocks. This is ideal for applications which may experience rough handling or in situations where the accelerometer must survive a high initial overload in order to make a low g measurement. These units feature a Wheatstone Bridge output with compensated temperature range of 20 to 80 °C.

FEATURES


- Miniature Triaxial
- Low Weight
- Static and Dynamic Measurement
- Frequency Response through 3000 Hz
- $\pm 1\%$ Non-Linearity
- -40 °C to +120 °C Operating Range
- 10,000 g Overrange Protection

APPLICATIONS

- Flight Test & Control
- Launch
- Robotics
- Shock Testing



dimensions



Model EGAXT3 Accelerometer

performance specifications

All values are typical at +24°C, 100Hz and 15Vdc excitation unless otherwise stated. Measurement Specialties reserves the right to update and change these specifications without notice.

Parameters											Notes
DYNAMIC											
Range (g)	±5	±10	±15	±25	±50	±100	±250	±500	±1000	±2500	
Sensitivity EGAXT (mV/g)	5.2-11.3	4.2-9.0	3.1-6.8	2.1-4.5	1.57-3.38	1.05-2.25	.52-1.13	.35-.75	.17-.38	.07-.15	
Frequency Response min. (Hz)	0-120	0-140	0-220	0-300	0-350	0-400	0-500	0-750	0-1000	0-1400	±1/2dB
Frequency Response nom. (Hz)	0-250	0-300	0-450	0-600	0-700	0-900	0-1000	0-1500	0-2000	0-3000	±1/2dB
Natural Frequency (Hz)	500	600	900	1200	1400	1700	2000	3000	4000	6000	
Non-Linearity (%FSO)	±1	±1	±1	±1	±1	±1	±1	±1	±1	±1	
Transverse Sensitivity (%)	<3	<3	<3	<3	<3	<3	<3	<3	<3	<3	
Damping Ratio	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	Nominal
Shock Limit (g)	10000	10000	10000	10000	10000	10000	10000	10000	10000	10000	All 3 Axes

ELECTRICAL

Zero Acceleration Output (mV)	±15										Differential
Excitation Voltage (Vdc)	15 (can be used from 2 to 15Vdc but lower excitation voltage will decrease sensitivity accordingly)										
Input Resistance (Ω)	1000										Nominal
Output Resistance (Ω)	450										Nominal
Insulation Resistance (MΩ)	>100										@50Vdc
Ground Isolation	Isolated from Mounting Surface										

ENVIRONMENTAL

Thermal Zero Shift	±2.5mV / 50°C (±2.5mV / 100°F)
Thermal Sensitivity Shift	+1 to -4% / 50°C (+1 to -4% / 100°F)
Operating Temperature	-40 to 120°C (-40 to 250°F)
Compensated Temperature	20 to 80°C (70 to 170°F), contact factory for other temperature compensation options
Storage Temperature	-40 to 120°C (-40 to 250°F)
Humidity	Epoxy Sealed

PHYSICAL

Case Material	Aluminum
Cable	12x Teflon Leads, 24 inch
Weight	6-11 grams
Mounting	Adhesive or Screw Mount Versions Available (-F configuration)
AWG	#34

Wiring color code:	X-axis: +Excitation = Red; -Excitation = Black; +Output = Green; -Output = White
	Y-axis: +Excitation = Red; -Excitation = Black; +Output = Blue; -Output = Yellow
	Z-axis: +Excitation = Red; -Excitation = Black; +Output = Brown; -Output = Orange

The information in this sheet has been carefully reviewed and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Furthermore, this information does not convey to the purchaser of such devices any license under the patent rights to the manufacturer. Measurement Specialties, Inc. reserves the right to make changes without further notice to any product herein. Measurement Specialties, Inc. makes no warranty, representation or guarantee regarding the suitability of its product for any particular purpose, nor does Measurement Specialties, Inc. assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Typical parameters can and do vary in different applications. All operating parameters must be validated for each customer application by customer's technical experts. Measurement Specialties, Inc. does not convey any license under its patent rights nor the rights of others.

ordering info

EGAXT3 - F - 100 - /L2M/C

Model	Range (X/Y/Z)	Options
		C
		L00F or L00M
		M00F or M00M
		V1 thru V15
Housing		S
F		

COMPENSATED TEMPERATURE RANGES: STANDARD	Z*	=	20°C TO 80°C (70°F TO 170°F)
		=	Non-Standard, contact factory
5 WIRE BRIDGE WIRING			
FOR ADJUSTABLE ZERO OFFSET:	5	=	5 wire
EXCITATION VOLTAGE:	STANDARD	=	15 Vdc
	V00	=	Replace "00" with Excitation between 1 and 15. If less than 15, Sensitivity (FSO) will decrease accordingly.
SPECIAL LEAD LENGTH:	L00F	=	Replace "00" with total length in feet
	L00M	=	Replace "00" with total length in meters
SPECIAL MODULE LOCATION:	M00F	=	Replace "00" with distance between sensor and module in feet
	M00M	=	Replace "00" with distance between sensor and module in meters
CONNECTOR WIRED TO CABLE:	C	=	Microtech male or equivalent *w/o mate)