

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

39980-0307

Status:


Active

Overview:

Eurostyle™ Terminal Blocks

Description:

5.08mm Pitch Beau™ Eurostyle™ Screw Clamp Plug, 7 Circuits



Documents:

3D Model

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                            |
|-------------------------------|----------------------------|
| Agency Certification          |                            |
| UL                            | E48521                     |
| General                       |                            |
| Product Family                | Terminal Blocks            |
| Series                        | 39980                      |
| Application                   | N/A                        |
| Comments                      | Gold plating available     |
| Component Type                | Plug                       |
| Overview                      | Eurostyle™ Terminal Blocks |
| Product Name                  | Eurostyle™ Pluggable       |
| Type                          | Euro Block                 |
| UPC                           | 800753317239               |
| Physical                      |                            |
| Circuits (Loaded)             | 7                          |
| Color - Resin                 | Black                      |
| Entry Angle                   | Horizontal                 |
| Flammability                  | 94V-0                      |
| Lock to Mating Part           | Yes                        |
| Material - Metal              | Brass                      |
| Material - Resin              | Nylon                      |
| Net Weight                    | 11.850/g                   |
| Number of Rows                | 1                          |
| Orientation                   | Vertical                   |
| PCB Retention                 | N/A                        |
| Panel Mount                   | No                         |
| Pitch - Mating Interface      | 5.08mm                     |
| Pitch - Termination Interface | 5.08mm                     |
| Polarized to Mating Part      | Yes                        |
| Shrouded                      | Fully                      |
| Stackable                     | No                         |
| Temperature Range - Operating | 110°C                      |
| Termination Interface: Style  | Surface Mount              |
| Wire Size AWG                 | 12, 14, 16, 18, 20, 22, 24 |
| Electrical                    |                            |
| Current - Maximum per Contact | 10A                        |
| Voltage - Maximum             | 300V                       |
| Material Info                 |                            |
| Old Part Number               | 980907                     |
| Reference - Drawing Numbers   |                            |
| Sales Drawing                 | SD-39980-010               |

EU RoHS

RoHS Compliant by Exemption

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS

50

Pb

Need more information on product environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

39980Series

Mates With

39980-0407

This document was generated on 12/19/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39980-0307](#)