







SCHEMATIC



Rating	DC30V 0.3A,DC16V 0.5A
Withstand Voltage	AC250V 1 minute
Insulation Resistance	$\geq 100M\Omega$ DC250V
Contact Resistance	$\leq 50m\Omega$
Soldering Temper.	245 $\pm$ 5 $^{\circ}$ C 5 Sec.
Mechanical Life	100000 cycles
Electrical Life	10000 cycles
Ambient Temper.Used	-25 $^{\circ}$ C - +65 $^{\circ}$ C
Ambient Humidity Used	<85%RH
Operating force	200 $\pm$ 80gf

NOTE: TOLERANCES UNLESS OTHERWISE SPECIFIED: $\pm 0.3mm$

RoHS Compliant

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 3-21-12

Rev. 0

Unit: mm

Checked By: *G. Gold*

Title:

PUSH SWITCH

CW P/N:

GPBS850L