

Product Information

ingun Prüfmittelbau GmbH
Max-Stromeyer-Straße 162
78467 Konstanz
Germany

Tel. +49 7531 8105-0
Fax +49 7531 8105-65
info@ingun.com
www.ingun.com


GKS-040 ... L

Balance-out of Contact Height in 40 mil grid

The INGUN L-version is now available in all four standard grid sizes: 40 / 50 / 75 and 100 Mil. When contacting e.g. component pins and test pads at the same time, then the usage of the 2mm longer L-version Probes (GKS-040 ... L) offers the same stroke conditions as the standard version (GKS-040). With this, different contacting heights can be balanced out. The L-version Probes in all four series, i.e. GKS-040 ... L, GKS-050 ... L, GKS-075 ... L and GKS-100 ... L, are compatible to the standard series and can therefore be used in the standard Receptacles of the applicable standard Probe series.


INGUN precision customizing now also in 40 mil grid

With this variant the renowned INGUN precision customizing with a reliable contacting area of the Probe points is now also possible in 40mil grid. The Probe with a 2mm longer plunger can be easily inserted in the Fixture using a UUT mounting plate as a permanently integrated guide plate and offering little wear.



Mechanical Data:

Recommended Working Stroke: 4.3 mm
Maximum Stroke: 6.35 mm
Spring Force at Working Stroke: 0.8 N



Contact us for further information.
Prices and availability on request.

Ordering Example:	Series	Tip Material 2 = Steel	Tip Style	Tip Diameter (1/100 mm)	Plating A = Gold	Spring Force (dN)	Collar Height (mm)	Special Designation
Test Probe:	GKS	0 4 0	2 9 7	0 4 0	A	0 8	0 0	L