






## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 12VDC, 12mA; DPST
5. CONTACT MATERIAL: GOLD
6. CONTACT RESISTANCE: 50 MILLI-OHM MAX.
7. INSULATION RESISTANCE: 500VDC, 100 MEGA-OHM MIN.
- ▲ 8. OPERATING FORCE: 200±100GF
9. OPERATING LIFE: 200,000 CYCLES
10. OPERATING TEMP: -20°C TO +70°C
- ▲ 11. LED COLORS: WHITE
12. TRAVEL: 2.20mm±0.20
13. 2002/95/EC (ROHS) COMPLIANT
14. ▲ DENOTES CRITICAL PARAMETER.



| ▲ LED SPECS               | UNITS | WHITE           |
|---------------------------|-------|-----------------|
| FORWARD CURRENT           | mA    | 20              |
| FORWARD VOLTAGE @20mA     | V     | 3.2 Typ-3.7 Max |
| LUMINOUS INTENSITY @ 10mA | mcd   | 78.5            |

|     |        |                               |         |     |
|-----|--------|-------------------------------|---------|-----|
| B   | 19589  | CHANGED DIMS: was 15.6 & 5.07 | 1/14/11 | BGL |
| A   | 18942  | New Release                   | 3/15/10 | rc  |
| REV | PCR NO | DESCRIPTION                   | DATE    | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|                  |           |    |         |     |
|------------------|-----------|----|---------|-----|
|                  |           |    |         |     |
| TITLE LP6OA2ASWW |           |    |         |     |
| SCALE            | DATE      | DR | DWG     | REV |
| 2=1              | 3/15/2010 | rc | B220006 | B   |