

## Product Information



### TYPICAL APPLICATIONS

- Fixing central heating pipes, shelving, brackets, dado rails and other woodwork.
- Securing light wall units and kitchen fittings.

### DESCRIPTION


All purpose cost effective fixing for medium and lightweight applications.

### SUITABLE FOR USE IN:

Brickwork  
Concrete

### FEATURES

1. Profiled Body for extra grip.
2. Anti-rotation fins.
3. Three colour coded sizes for screws from 3-6 mm (No. 4-14).
4. Additional sizes for screws 3-10 mm (No. 4-20).



## PLASTIC PLUGS

| DESCRIPTION                      | SCREW RANGE<br>(mm)       | PLUG LENGTH<br>(mm) | HOLE DIAMETER<br>(mm)<br>(d <sub>0</sub> ) | OPTIONS    | BOX/PACK QUANTITY | PRODUCT CODE |          |        |        | NEW CODE     |
|----------------------------------|---------------------------|---------------------|--------------------------------------------|------------|-------------------|--------------|----------|--------|--------|--------------|
|                                  |                           |                     |                                            |            |                   | CLIP         |          | PACKS  | BOX    |              |
|                                  |                           |                     |                                            |            |                   | CARDED       | UNCARDED |        |        |              |
| YELLOW                           | 3.0 - 5.0<br>No. 4 - 10   | 25                  | 5                                          |            | 20                |              | 67-128   |        |        | YEL-20-NC    |
|                                  |                           |                     |                                            |            | 100               |              | 67-125   |        |        | YEL-100-NC   |
|                                  |                           |                     |                                            |            | 100               | 67-126       |          |        |        | YEL-100-C    |
|                                  |                           |                     |                                            |            | 300               |              |          | 67-900 |        | YEL-300      |
|                                  |                           |                     |                                            |            | 1000              |              |          |        | 67-910 | YEL-1000     |
| RED                              | 3.5 - 5.5<br>No. 6 - 12   | 35                  | 6                                          |            | 20                |              | 67-138   |        |        | RED-20-NC    |
|                                  |                           |                     |                                            | with drill | 50                |              |          | 67-300 |        | RED-10/50+D  |
|                                  |                           |                     |                                            |            | 100               |              | 67-130   |        |        | RED-100-NC   |
|                                  |                           |                     |                                            |            | 100               | 67-134       |          |        |        | RED-100-C    |
|                                  |                           |                     |                                            |            | 300               |              |          | 67-902 |        | RED-300      |
|                                  |                           |                     |                                            |            | 1000              |              |          |        | 67-913 | RED-1000     |
| BROWN                            | 5.0 - 6.0<br>No. 10 - 14  | 45                  | 7                                          |            | 20                |              | 67-237   |        |        | BRN-20-NC    |
|                                  |                           |                     |                                            | with drill | 50                |              |          | 67-310 |        | BRN-10/50+D  |
|                                  |                           |                     |                                            |            | 100               |              | 67-231   |        |        | BRN-100-NC   |
|                                  |                           |                     |                                            |            | 100               | 67-233       |          |        |        | BRN-100-C    |
|                                  |                           |                     |                                            | with drill | 100               |              |          | 67-315 |        | BRN-10/100+D |
|                                  |                           |                     |                                            |            | 300               |              |          | 67-904 |        | BRN-300      |
|                                  | 1000                      |                     |                                            |            | 67-916            | BRN-1000     |          |        |        |              |
| ASSORTED yel-<br>low, red, brown | 3.0 - 6.0<br>No 4 - 14    | 25 - 45             | 5 - 7                                      |            | 300               |              |          | 67-905 |        | AST          |
| GREEN                            | 3.0 - 4,5<br>No. 4 - 8    | 20                  | 4.5                                        |            | 10 x 10           |              | 67-008   |        |        | PLP-GRN      |
| PINK                             | 3.5 - 5.0<br>No. 6 - 10   | 25                  | 5.5                                        |            | 10 x 10           |              | 67-012   |        |        | PLP-PNK      |
| ORANGE                           | 4.5 - 5.5<br>No. 8 - 12   | 25                  | 6.5                                        |            | 10 x 10           |              | 67-016   |        |        | PLP-ORG      |
| GREY                             | 4.5 - 5.0<br>No. 8 - 10   | 35                  | 5.5                                        |            | 10 x 10           |              | 67-020   |        |        | PLP-GRY      |
| WHITE                            | 4.5 - 5.5<br>No. 10 - 14  | 35                  | 6.5                                        |            | 10 x 10           |              | 67-024   |        |        | PLP-WHT      |
| BLUE                             | 5.0 - 6.0<br>No. 10 - 14  | 35                  | 8.0                                        |            | 10 x 10           |              | 67-028   |        |        | PLP-BLU      |
| RED                              | 4.5 - 5.0<br>No. 8 - 10   | 35                  | 5.5                                        |            | 10 x 10           |              |          |        | 67-021 | PLP-RED      |
| BROWN                            | 5.0 - 6.0<br>No. 10 - 14  | 35                  | 8.0                                        |            | 10 x 10           |              |          |        | 67-029 | PLP-BRN      |
| YELLOW                           | 8.0 - 10.0<br>No. 16 - 20 | 50                  | 11                                         |            | 10 x 10           |              |          |        | 67-032 | PLP-YEL      |
| BROWN                            | 5.0 - 6.0<br>No. 10 - 14  | 35                  | 8.0                                        |            | 22 x 50           |              |          |        | 67-965 | PLP-22       |
| BROWN                            | 5.0 - 6.0<br>No. 10 - 14  | 35                  | 8.0                                        |            | 44 x 50           |              |          |        | 67-960 | PLP-44       |