

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19

© COPYRIGHT 19




BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	O	RELEASED	'95 7/04	JW	BM
	A	REVISED(FC00-0013-01)	15/FEB/'01	MS	CS



SECTION A-A

LANCE DETAIL

PBT	BLUE	85228-2	Ⓐ
PBT	NATURAL	85228-1	
MATERIAL	COLOR	PART NO	



NOTE:

- Ⓐ TO BE MEASURED BETWEEN -A- AND 2
- Ⓐ TO BE MATED WITH TAB HSG SMOOTHLY
- 3 APPLIED RECEPTACLE CONTACT PART NUMBERS
.070 SERIES, 173630, 173631
.250 SERIES, 170032, 170258, 170384
- 4 APPLIED TAB HSG P/N : 85110

APPLICABLE TAB CONTACT			
WIRE RANGE		TML P/N	CURRENT (A)
AWG	mm ²		
24-22	0.2-0.35	173633	3
20-16	0.5-1.25	173645	10
16-14	1.25-2.0	85099	10

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
MM

3rd ANGLE PROJECTION

MATERIAL

SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 <XX<10 ± 0.2
10<XX<30 ± 0.25
30<XX ± 0.3
ANGLES ± 3°

FINISH

SEE TABLE

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

AMPAMP KOREA.
kyungsan, korea

NAME

070/250 19P HYBRID REC HSG

SIZE

CAGE CODE

DRAWING NO

A3

00779

C= 85228

SCALE 2/1

SHEET 1 OF 1

REV A